

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244949

Luminaire Tested: **LSR8B50D010 EC8B50930 8LBS0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244949
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B50D010 EC8B50930 8LBS0WMH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4886.5 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244949

CATALOG NUMBER: LSR8B50D010 EC8B50930 8LBS0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244949

CATALOG NUMBER: LSR8B50D010 EC8B50930 8LBS0W/MH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 101 | 102 | 100 | 98 | 99 | 97 | 95 | 95 | 94 | 92 | 91 |
| 2 | 105 | 99 | 94 | 89 | 102 | 97 | 92 | 88 | 94 | 90 | 86 | 90 | 87 | 85 | 88 | 85 | 83 | 81 |
| 3 | 98 | 90 | 83 | 78 | 95 | 88 | 82 | 78 | 85 | 80 | 76 | 83 | 79 | 75 | 80 | 77 | 74 | 72 |
| 4 | 91 | 82 | 75 | 69 | 89 | 80 | 74 | 69 | 78 | 72 | 68 | 76 | 71 | 67 | 74 | 70 | 66 | 65 |
| 5 | 85 | 74 | 67 | 62 | 83 | 73 | 67 | 61 | 71 | 65 | 61 | 70 | 64 | 60 | 68 | 63 | 60 | 58 |
| 6 | 79 | 68 | 61 | 55 | 77 | 67 | 60 | 55 | 66 | 59 | 55 | 64 | 58 | 54 | 63 | 58 | 54 | 52 |
| 7 | 74 | 63 | 55 | 50 | 72 | 62 | 55 | 50 | 60 | 54 | 49 | 59 | 53 | 49 | 58 | 53 | 49 | 47 |
| 8 | 69 | 58 | 50 | 45 | 68 | 57 | 50 | 45 | 56 | 49 | 45 | 55 | 49 | 45 | 54 | 48 | 45 | 43 |
| 9 | 65 | 53 | 46 | 41 | 64 | 53 | 46 | 41 | 52 | 45 | 41 | 51 | 45 | 41 | 50 | 45 | 41 | 39 |
| 10 | 61 | 50 | 43 | 38 | 60 | 49 | 42 | 38 | 48 | 42 | 38 | 47 | 42 | 38 | 46 | 41 | 37 | 36 |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244949

CATALOG NUMBER: LSR8B50D010 EC8B50930 8LBS0WMH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 260.8 | 5.3 |
| 10°-20° | 738.2 | 15.1 |
| 20°-30° | 1099.1 | 22.5 |
| 30°-40° | 1248.5 | 25.6 |
| 40°-50° | 1020.6 | 20.9 |
| 50°-60° | 399.9 | 8.2 |
| 60°-70° | 93.2 | 1.9 |
| 70°-80° | 22.5 | 0.5 |
| 80°-90° | 3.6 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2098.2 | 42.9 |
| 0°-40° | 3346.7 | 68.5 |
| 0°-60° | 4767.2 | 97.6 |
| 0°-90° | 4886.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 4886.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2771 | |
| 5° | 2751 | 261 |
| 15° | 2618 | 738 |
| 25° | 2391 | 1099 |
| 35° | 2006 | 1249 |
| 45° | 1355 | 1021 |
| 55° | 416 | 400 |
| 65° | 87 | 93 |
| 75° | 21 | 22 |
| 85° | 3 | 4 |
| 90° | 0 | |



TEST NUMBER: P244949

CATALOG NUMBER: LSR8B50D010 EC8B50930 8LBS0WMH

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 2770.6 |
| 2.5° | 2766.2 |
| 5° | 2751.4 |
| 7.5° | 2726.5 |
| 10° | 2695.6 |
| 12.5° | 2657.3 |
| 15° | 2617.6 |
| 17.5° | 2570.7 |
| 20° | 2519.2 |
| 22.5° | 2458.9 |
| 25° | 2391.3 |
| 27.5° | 2312.0 |
| 30° | 2222.3 |
| 32.5° | 2120.9 |
| 35° | 2006.3 |
| 37.5° | 1879.8 |
| 40° | 1738.8 |
| 42.5° | 1568.3 |
| 45° | 1355.2 |
| 47.5° | 1105.3 |
| 50° | 845.1 |
| 52.5° | 607.0 |
| 55° | 416.0 |
| 57.5° | 272.0 |
| 60° | 182.3 |
| 62.5° | 124.9 |
| 65° | 86.8 |
| 67.5° | 57.3 |
| 70° | 38.2 |
| 72.5° | 26.5 |
| 75° | 20.6 |
| 77.5° | 14.7 |
| 80° | 8.9 |
| 82.5° | 4.4 |
| 85° | 2.9 |
| 87.5° | 1.5 |
| 90° | 0.0 |

(END OF REPORT)