

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250537

Luminaire Tested: **LSR8B150D010 EC8B1509730 8LBM0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250537
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14005)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B150D010 EC8B1509730 8LBM0GPH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10367.0 lumens
Efficiency: N/A
Efficacy: 65.4 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 158.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250537

CATALOG NUMBER: LSR8B150D010 EC8B1509730 8LBM0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250537

CATALOG NUMBER: LSR8B150D010 EC8B1509730 8LBM0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250537

CATALOG NUMBER: LSR8B150D010 EC8B1509730 8LBM0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1170.5	11.3
10°-20°	2783.1	26.8
20°-30°	3467.3	33.4
30°-40°	2338.8	22.6
40°-50°	553.0	5.3
50°-60°	40.4	0.4
60°-70°	7.2	0.1
70°-80°	5.3	0.1
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7421.0	71.6
0°-40°	9759.8	94.1
0°-60°	10353.3	99.9
0°-90°	10367.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10367.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13148	
5°	12767	###
15°	9884	2783
25°	7686	3467
35°	3749	2339
45°	601	553
55°	18	40
65°	0	7
75°	14	5
85°	4	1
90°	0	



TEST NUMBER: P250537

CATALOG NUMBER: LSR8B150D010 EC8B1509730 8LBM0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	13148.1
2.5°	13125.7
5°	12766.9
7.5°	12116.7
10°	11314.0
12.5°	10556.2
15°	9883.5
17.5°	9305.0
20°	8771.4
22.5°	8260.2
25°	7686.2
27.5°	6937.3
30°	6022.5
32.5°	4914.9
35°	3749.0
37.5°	2681.7
40°	1748.9
42.5°	1044.9
45°	600.9
47.5°	336.3
50°	165.9
52.5°	76.3
55°	17.9
57.5°	4.5
60°	9.0
62.5°	13.5
65°	0.0
67.5°	9.0
70°	4.5
72.5°	4.5
75°	13.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	4.5
87.5°	0.0
90°	0.0

(END OF REPORT)