

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245729

Luminaire Tested: **LSR8B50D010 EC8B50950 8LBM0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245729
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201629)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B50D010 EC8B50950 8LBM0GPH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4469.0 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245729

CATALOG NUMBER: LSR8B50D010 EC8B50950 8LBM0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245729

CATALOG NUMBER: LSR8B50D010 EC8B50950 8LBM0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	174805
5°	170368
10°	152762
15°	136025
20°	124117
25°	112715
30°	92439
35°	60867
40°	30331
45°	11277
50°	3435
55°	387
60°	234
65°	0
70°	162
75°	667
80°	0
85°	637



TEST NUMBER: P245729

CATALOG NUMBER: LSR8B50D010 EC8B50950 8LBM0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	504.7	11.3
10°-20°	1199.9	26.8
20°-30°	1494.6	33.4
30°-40°	1008.6	22.6
40°-50°	238.4	5.3
50°-60°	17.3	0.4
60°-70°	3.0	0.1
70°-80°	2.2	0.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3199.1	71.6
0°-40°	4207.7	94.2
0°-60°	4463.3	99.9
0°-90°	4469.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4469.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5669	
5°	5504	505
15°	4261	1200
25°	3313	1495
35°	1617	1009
45°	259	238
55°	7	17
65°	0	3
75°	6	2
85°	2	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P245729

CATALOG NUMBER: LSR8B50D010 EC8B50950 8LBM0GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5668.8
2.5°	5659.8
5°	5503.9
7.5°	5223.3
10°	4878.7
12.5°	4550.5
15°	4260.9
17.5°	4011.3
20°	3782.3
22.5°	3560.4
25°	3312.8
27.5°	2990.2
30°	2596.1
32.5°	2119.4
35°	1616.9
37.5°	1157.0
40°	753.5
42.5°	450.9
45°	258.6
47.5°	144.9
50°	71.6
52.5°	33.0
55°	7.2
57.5°	1.8
60°	3.8
62.5°	5.6
65°	0.0
67.5°	3.8
70°	1.8
72.5°	1.8
75°	5.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	1.8
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245729

CATALOG NUMBER: LSR8B50D010 EC8B50950 8LBM0GPH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)