

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245372

Luminaire Tested: **LSR8B20D010 EC8B20927 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245372
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B20D010 EC8B20927 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 2700 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1827.0 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245372

CATALOG NUMBER: LSR8B20D010 EC8B20927 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P245372

CATALOG NUMBER: LSR8B20D010 EC8B20927 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57		66	60	56		64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47		56	51	47		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39		49	43	39		48	43	39	38

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P245372

CATALOG NUMBER: LSR8B20D010 EC8B20927 8LBS0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	5.4
10°-20°	292.7	16.0
20°-30°	453.3	24.8
30°-40°	491.0	26.9
40°-50°	353.3	19.3
50°-60°	118.2	6.5
60°-70°	17.9	1.0
70°-80°	1.5	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	844.8	46.2
0°-40°	1335.8	73.1
0°-60°	1807.4	98.9
0°-90°	1827.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1827.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1035	
5°	1035	99
15°	1036	293
25°	990	453
35°	792	491
45°	465	353
55°	120	118
65°	16	18
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P245372

CATALOG NUMBER: LSR8B20D010 EC8B20927 8LBS0WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1034.9
2.5°	1034.9
5°	1034.9
7.5°	1035.3
10°	1035.9
12.5°	1036.9
15°	1035.9
17.5°	1031.6
20°	1022.2
22.5°	1007.9
25°	989.9
27.5°	961.3
30°	916.9
32.5°	858.7
35°	791.6
37.5°	719.1
40°	640.4
42.5°	555.8
45°	465.3
47.5°	367.5
50°	272.8
52.5°	187.2
55°	119.5
57.5°	71.4
60°	42.9
62.5°	25.9
65°	15.9
67.5°	8.0
70°	3.7
72.5°	1.6
75°	1.0
77.5°	1.0
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)