

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244946

Luminaire Tested: **LSR8B20D010 EC8B20930 8LBS0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244946
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B20D010 EC8B20930 8LBS0WMH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1925.9 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244946

CATALOG NUMBER: LSR8B20D010 EC8B20930 8LBS0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244946

CATALOG NUMBER: LSR8B20D010 EC8B20930 8LBS0W/MH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86		90	87	85		88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76		83	79	75		80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68		76	71	67		74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61		70	64	60		68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55		64	58	54		63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49		59	53	49		58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45		55	49	45		54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41		51	45	41		50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38		47	42	38		46	41	37	36

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244946

CATALOG NUMBER: LSR8B20D010 EC8B20930 8LBS0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.8	5.3
10°-20°	291.0	15.1
20°-30°	433.2	22.5
30°-40°	492.1	25.6
40°-50°	402.2	20.9
50°-60°	157.6	8.2
60°-70°	36.7	1.9
70°-80°	8.8	0.5
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	827.0	42.9
0°-40°	1319.1	68.5
0°-60°	1878.9	97.6
0°-90°	1925.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1925.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1092	
5°	1084	103
15°	1032	291
25°	942	433
35°	791	492
45°	534	402
55°	164	158
65°	34	37
75°	8	9
85°	1	1
90°	0	



TEST NUMBER: P244946

CATALOG NUMBER: LSR8B20D010 EC8B20930 8LBS0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1092.0
2.5°	1090.2
5°	1084.5
7.5°	1074.6
10°	1062.4
12.5°	1047.4
15°	1031.7
17.5°	1013.2
20°	992.9
22.5°	969.1
25°	942.5
27.5°	911.3
30°	875.8
32.5°	835.9
35°	790.8
37.5°	740.9
40°	685.3
42.5°	618.1
45°	534.0
47.5°	435.6
50°	333.0
52.5°	239.2
55°	163.9
57.5°	107.2
60°	71.9
62.5°	49.2
65°	34.2
67.5°	22.6
70°	15.0
72.5°	10.4
75°	8.1
77.5°	5.8
80°	3.5
82.5°	1.8
85°	1.1
87.5°	0.6
90°	0.0

(END OF REPORT)