

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246671

Luminaire Tested: **LSR8B50D010 EC8B509727 8LBN0MW**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246671  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B50D010 EC8B509727 8LBN0MW  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 2700 CCT WITH MATTE WHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3530.0 lumens  
Efficiency: N/A  
Efficacy: 66.6 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 53  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246671

CATALOG NUMBER: LSR8B50D010 EC8B509727 8LBN0MW

### Luminous Intensity Polar Plot





TEST NUMBER: P246671

CATALOG NUMBER: LSR8B50D010 EC8B509727 8LBN0MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98		98	97	95		95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71		78	74	70		76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65		73	68	64		71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55		64	59	55		63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53	48	45	43

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P246671

CATALOG NUMBER: LSR8B50D010 EC8B509727 8LBN0MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	337.7	9.6
10°-20°	781.1	22.1
20°-30°	928.9	26.3
30°-40°	656.7	18.6
40°-50°	339.0	9.6
50°-60°	232.4	6.6
60°-70°	150.9	4.3
70°-80°	79.1	2.2
80°-90°	24.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2047.7	58.0
0°-40°	2704.4	76.6
0°-60°	3275.7	92.8
0°-90°	3530.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3530.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3702	
5°	3661	338
15°	2773	781
25°	2058	929
35°	1042	657
45°	424	339
55°	257	232
65°	152	151
75°	74	79
85°	20	23
90°	0	2
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P246671

CATALOG NUMBER: LSR8B50D010 EC8B509727 8LBN0MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3701.9
2.5°	3701.9
5°	3661.3
7.5°	3526.7
10°	3298.4
12.5°	3026.0
15°	2773.0
17.5°	2564.8
20°	2390.8
22.5°	2226.2
25°	2057.6
27.5°	1846.0
30°	1587.9
32.5°	1310.2
35°	1042.1
37.5°	802.9
40°	618.3
42.5°	497.6
45°	424.0
47.5°	370.5
50°	329.0
52.5°	292.5
55°	257.3
57.5°	226.4
60°	200.8
62.5°	174.0
65°	151.6
67.5°	131.4
70°	105.7
72.5°	90.8
75°	73.6
77.5°	59.7
80°	46.0
82.5°	34.2
85°	20.4
87.5°	11.8
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246671

CATALOG NUMBER: LSR8B50D010 EC8B509727 8LBN0MW

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)