

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245535

Luminaire Tested: **LSR8B30D010 EC8B30830 8LBW0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245535  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B30D010 EC8B30830 8LBW0GPH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 3000 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2664.0 lumens  
Efficiency: N/A  
Efficacy: 98.3 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 27.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245535

CATALOG NUMBER: LSR8B30D010 EC8B30830 8LBW0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P245535

CATALOG NUMBER: LSR8B30D010 EC8B30830 8LBW0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66	74	70	66	73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51	60	55	51	59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	63964
5°	62453
10°	60495
15°	59621
20°	58917
25°	57654
30°	54001
35°	44093
40°	26322
45°	15813
50°	11394
55°	7758
60°	4866
65°	2386
70°	604
75°	226
80°	178
85°	0



TEST NUMBER: P245535

CATALOG NUMBER: LSR8B30D010 EC8B30830 8LBW0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.8	7.1
10°-20°	527.0	19.8
20°-30°	774.0	29.1
30°-40°	701.6	26.3
40°-50°	300.3	11.3
50°-60°	132.9	5.0
60°-70°	35.4	1.3
70°-80°	2.8	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1490.8	56.0
0°-40°	2192.4	82.3
0°-60°	2625.7	98.6
0°-90°	2664.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2664.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2074	
5°	2018	190
15°	1868	527
25°	1694	774
35°	1171	702
45°	363	300
55°	144	133
65°	33	35
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P245535

CATALOG NUMBER: LSR8B30D010 EC8B30830 8LBW0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2074.3
2.5°	2058.0
5°	2017.6
7.5°	1971.4
10°	1932.0
12.5°	1899.3
15°	1867.6
17.5°	1833.9
20°	1795.4
22.5°	1750.2
25°	1694.5
27.5°	1619.5
30°	1516.6
32.5°	1372.3
35°	1171.3
37.5°	907.8
40°	653.9
42.5°	472.2
45°	362.6
47.5°	292.3
50°	237.5
52.5°	188.5
55°	144.3
57.5°	107.7
60°	78.9
62.5°	54.8
65°	32.7
67.5°	14.4
70°	6.7
72.5°	3.8
75°	1.9
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)