

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244079

Luminaire Tested: **LSR8B50D010 EC8B509727 8LBS0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244079
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B50D010 EC8B509727 8LBSOLI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 2700 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4321.0 lumens
Efficiency: N/A
Efficacy: 81.5 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244079

CATALOG NUMBER: LSR8B50D010 EC8B509727 8LBSOLI

Luminous Intensity Polar Plot





TEST NUMBER: P244079

CATALOG NUMBER: LSR8B50D010 EC8B509727 8LBS0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88	91	88	86	88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63	71	66	62	69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47	56	51	46	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39	49	43	39	48	43	39	37

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244079

CATALOG NUMBER: LSR8B50D010 EC8B509727 8LBSOLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	230.4	5.3
10°-20°	688.1	15.9
20°-30°	1066.0	24.7
30°-40°	1157.7	26.8
40°-50°	841.3	19.5
50°-60°	285.9	6.6
60°-70°	45.6	1.1
70°-80°	4.9	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1984.6	45.9
0°-40°	3142.4	72.7
0°-60°	4269.6	98.8
0°-90°	4321.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4321.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2409	
5°	2410	230
15°	2435	688
25°	2327	1066
35°	1866	1158
45°	1108	841
55°	291	286
65°	40	46
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P244079

CATALOG NUMBER: LSR8B50D010 EC8B509727 8LBSOLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2409.2
2.5°	2409.2
5°	2410.4
7.5°	2414.2
10°	2421.6
12.5°	2430.3
15°	2435.2
17.5°	2430.3
20°	2410.4
22.5°	2374.5
25°	2327.4
27.5°	2256.8
30°	2155.1
32.5°	2020.1
35°	1866.4
37.5°	1699.1
40°	1516.9
42.5°	1319.9
45°	1107.9
47.5°	879.9
50°	653.1
52.5°	447.4
55°	291.2
57.5°	177.2
60°	106.6
62.5°	65.7
65°	39.7
67.5°	22.3
70°	9.9
72.5°	6.2
75°	3.7
77.5°	2.5
80°	2.5
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0

(END OF REPORT)