

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243969

Luminaire Tested: **LSR8B30D010 EC8B30850 8LBM0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243969
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-11)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30850 8LBM0LI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3250.0 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.72
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243969

CATALOG NUMBER: LSR8B30D010 EC8B30850 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243969

CATALOG NUMBER: LSR8B30D010 EC8B30850 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	73	80	75	72		79	75	72		77	74	71	70
7	86	78	72	69	85	77	72	68	76	71	68		75	71	68		74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	60	59
10	76	67	62	58	75	67	61	58	66	61	58		65	61	58		64	60	58	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	174830
5°	167313
10°	148954
15°	119661
20°	93724
25°	75673
30°	58637
35°	33398
40°	12599
45°	5434
50°	2188
55°	817
60°	438
65°	299
70°	180
75°	119
80°	0
85°	0



TEST NUMBER: P243969

CATALOG NUMBER: LSR8B30D010 EC8B30850 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	496.1	15.3
10°-20°	1040.9	32.0
20°-30°	1018.5	31.3
30°-40°	563.5	17.3
40°-50°	109.1	3.4
50°-60°	16.7	0.5
60°-70°	4.1	0.1
70°-80°	1.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2555.5	78.6
0°-40°	3119.0	96.0
0°-60°	3244.8	99.8
0°-90°	3250.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3250.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5670	
5°	5405	496
15°	3748	1041
25°	2224	1019
35°	887	564
45°	125	109
55°	15	17
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P243969

CATALOG NUMBER: LSR8B30D010 EC8B30850 8LBM0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5669.6
2.5°	5591.6
5°	5405.2
7.5°	5143.9
10°	4757.1
12.5°	4267.9
15°	3748.3
17.5°	3261.2
20°	2856.1
22.5°	2520.8
25°	2224.1
27.5°	1944.5
30°	1646.8
32.5°	1297.4
35°	887.2
37.5°	533.7
40°	313.0
42.5°	195.5
45°	124.6
47.5°	78.0
50°	45.6
52.5°	25.3
55°	15.2
57.5°	9.1
60°	7.1
62.5°	5.1
65°	4.1
67.5°	3.0
70°	2.0
72.5°	1.0
75°	1.0
77.5°	1.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)