

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251494

Luminaire Tested: **LSR8B60D010 EC8B60930 8LBS0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251494
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-18)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B60930 8LBS0MW
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 3000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6417.7 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251494

CATALOG NUMBER: LSR8B60D010 EC8B60930 8LBS0MW

Luminous Intensity Polar Plot





TEST NUMBER: P251494

CATALOG NUMBER: LSR8B60D010 EC8B60930 8LBS0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	98	96	97	95	93	94	92	91	89
2	103	97	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	67	63	61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103172
5°	102758
10°	101607
15°	100197
20°	98889
25°	97384
30°	95269
35°	92074
40°	87033
45°	75801
50°	54814
55°	34128
60°	22227
65°	18256
70°	16842
75°	18241
80°	18575
85°	16487



TEST NUMBER: P251494

CATALOG NUMBER: LSR8B60D010 EC8B60930 8LBS0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	314.5	4.9
10°-20°	885.4	13.8
20°-30°	1317.1	20.5
30°-40°	1524.6	23.8
40°-50°	1308.2	20.4
50°-60°	601.5	9.4
60°-70°	255.4	4.0
70°-80°	158.2	2.5
80°-90°	52.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2517.0	39.2
0°-40°	4041.6	63.0
0°-60°	5951.3	92.7
0°-90°	6417.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6417.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3346	
5°	3320	314
15°	3139	885
25°	2862	1317
35°	2446	1525
45°	1738	1308
55°	635	602
65°	250	255
75°	153	158
85°	47	53
90°	0	



TEST NUMBER: P251494

CATALOG NUMBER: LSR8B60D010 EC8B60930 8LBS0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3345.8
2.5°	3338.3
5°	3319.7
7.5°	3288.0
10°	3245.0
12.5°	3194.6
15°	3138.6
17.5°	3078.8
20°	3013.5
22.5°	2942.5
25°	2862.2
27.5°	2772.7
30°	2675.6
32.5°	2567.2
35°	2445.9
37.5°	2315.2
40°	2162.1
42.5°	1973.5
45°	1738.2
47.5°	1448.9
50°	1142.6
52.5°	858.9
55°	634.8
57.5°	466.8
60°	360.4
62.5°	295.0
65°	250.2
67.5°	214.7
70°	186.8
72.5°	169.9
75°	153.1
77.5°	130.7
80°	104.6
82.5°	74.7
85°	46.6
87.5°	20.5
90°	0.0

(END OF REPORT)