

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245805

Luminaire Tested: **LSR8B30D010 EC8B30927 8LBS0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245805  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B30D010 EC8B30927 8LBS0GPH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 2700 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2399.7 lumens  
Efficiency: N/A  
Efficacy: 88.5 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 27.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245805

CATALOG NUMBER: LSR8B30D010 EC8B30927 8LBS0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P245805

CATALOG NUMBER: LSR8B30D010 EC8B30927 8LBS0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50	59	54	50	58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45	55	49	45	54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P245805

CATALOG NUMBER: LSR8B30D010 EC8B30927 8LBS0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	129.6	5.4
10°-20°	366.6	15.3
20°-30°	545.8	22.7
30°-40°	620.4	25.9
40°-50°	507.3	21.1
50°-60°	189.1	7.9
60°-70°	34.6	1.4
70°-80°	5.4	0.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1042.1	43.4
0°-40°	1662.5	69.3
0°-60°	2359.0	98.3
0°-90°	2399.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2399.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1377	
5°	1368	130
15°	1300	367
25°	1187	546
35°	996	620
45°	675	507
55°	194	189
65°	31	35
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P245805

CATALOG NUMBER: LSR8B30D010 EC8B30927 8LBS0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1377.3
2.5°	1375.1
5°	1368.0
7.5°	1355.4
10°	1339.0
12.5°	1320.2
15°	1299.8
17.5°	1276.3
20°	1251.3
22.5°	1221.5
25°	1187.1
27.5°	1148.0
30°	1103.3
32.5°	1052.4
35°	996.1
37.5°	935.8
40°	866.0
42.5°	780.0
45°	675.0
47.5°	548.9
50°	416.6
52.5°	293.6
55°	194.2
57.5°	122.2
60°	75.9
62.5°	48.6
65°	31.3
67.5°	18.0
70°	10.1
72.5°	6.3
75°	4.7
77.5°	3.2
80°	2.4
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)