

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251298

Luminaire Tested: **LSR8B60D010 EC8B60935 8LBS0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251298  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B60D010 EC8B60935 8LBS0GPH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 3500 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5268.0 lumens  
Efficiency: N/A  
Efficacy: 88.5 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251298

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBS0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P251298

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBS0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50	59	54	50	58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45	55	49	45	54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	93243
5°	92961
10°	92045
15°	91099
20°	90147
25°	88670
30°	86247
35°	82313
40°	76535
45°	64620
50°	43871
55°	22919
60°	10281
65°	5020
70°	2011
75°	1227
80°	923
85°	601



TEST NUMBER: P251298

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBS0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	284.6	5.4
10°-20°	804.9	15.3
20°-30°	1198.2	22.7
30°-40°	1362.1	25.9
40°-50°	1113.8	21.1
50°-60°	415.1	7.9
60°-70°	75.9	1.4
70°-80°	11.8	0.2
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2287.7	43.4
0°-40°	3649.8	69.3
0°-60°	5178.7	98.3
0°-90°	5268.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5268.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3024	
5°	3003	285
15°	2854	805
25°	2606	1198
35°	2187	1362
45°	1482	1114
55°	426	415
65°	69	76
75°	10	12
85°	2	2
90°	0	



TEST NUMBER: P251298

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBS0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3023.8
2.5°	3018.7
5°	3003.2
7.5°	2975.7
10°	2939.6
12.5°	2898.3
15°	2853.6
17.5°	2802.1
20°	2747.1
22.5°	2681.7
25°	2606.1
27.5°	2520.1
30°	2422.2
32.5°	2310.4
35°	2186.6
37.5°	2054.3
40°	1901.3
42.5°	1712.2
45°	1481.8
47.5°	1205.1
50°	914.5
52.5°	644.6
55°	426.3
57.5°	268.2
60°	166.7
62.5°	106.6
65°	68.8
67.5°	39.5
70°	22.3
72.5°	13.8
75°	10.3
77.5°	6.9
80°	5.2
82.5°	1.7
85°	1.7
87.5°	0.0
90°	0.0

(END OF REPORT)