

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244371

Luminaire Tested: **LSR8B30D010 EC8B30930 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244371
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27944)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30930 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2313.8 lumens
Efficiency: N/A
Efficacy: 85.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244371

CATALOG NUMBER: LSR8B30D010 EC8B30930 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P244371

CATALOG NUMBER: LSR8B30D010 EC8B30930 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 101 | | 101 | 100 | 98 | | 98 | 97 | 96 | 94 |
| 2 | 108 | 104 | 100 | 96 | 106 | 102 | 98 | 95 | 99 | 96 | 93 | | 96 | 93 | 91 | | 93 | 91 | 89 | 88 |
| 3 | 103 | 97 | 92 | 88 | 101 | 95 | 91 | 87 | 93 | 89 | 86 | | 90 | 87 | 85 | | 88 | 86 | 83 | 82 |
| 4 | 98 | 91 | 85 | 81 | 96 | 90 | 85 | 81 | 87 | 83 | 80 | | 85 | 82 | 79 | | 84 | 80 | 78 | 76 |
| 5 | 93 | 85 | 79 | 75 | 92 | 84 | 79 | 75 | 82 | 78 | 74 | | 81 | 77 | 74 | | 79 | 76 | 73 | 72 |
| 6 | 89 | 80 | 74 | 70 | 87 | 79 | 74 | 70 | 78 | 73 | 69 | | 76 | 72 | 69 | | 75 | 71 | 69 | 67 |
| 7 | 85 | 76 | 70 | 66 | 83 | 75 | 69 | 65 | 74 | 69 | 65 | | 72 | 68 | 65 | | 71 | 67 | 64 | 63 |
| 8 | 81 | 71 | 66 | 62 | 79 | 71 | 65 | 61 | 70 | 65 | 61 | | 69 | 64 | 61 | | 68 | 64 | 61 | 59 |
| 9 | 77 | 68 | 62 | 58 | 76 | 67 | 62 | 58 | 66 | 61 | 58 | | 65 | 61 | 58 | | 64 | 60 | 57 | 56 |
| 10 | 74 | 64 | 59 | 55 | 73 | 64 | 58 | 55 | 63 | 58 | 55 | | 62 | 58 | 54 | | 61 | 57 | 54 | 53 |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244371

CATALOG NUMBER: LSR8B30D010 EC8B30930 8LBN0H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 297.0 | 12.8 |
| 10°-20° | 663.7 | 28.7 |
| 20°-30° | 754.6 | 32.6 |
| 30°-40° | 443.2 | 19.2 |
| 40°-50° | 118.9 | 5.1 |
| 50°-60° | 28.2 | 1.2 |
| 60°-70° | 6.5 | 0.3 |
| 70°-80° | 1.5 | 0.1 |
| 80°-90° | 0.1 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1715.4 | 74.1 |
| 0°-40° | 2158.6 | 93.3 |
| 0°-60° | 2305.7 | 99.7 |
| 0°-90° | 2313.8 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2313.8 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3532 | |
| 5° | 3282 | 297 |
| 15° | 2374 | 664 |
| 25° | 1665 | 755 |
| 35° | 690 | 443 |
| 45° | 142 | 119 |
| 55° | 28 | 28 |
| 65° | 6 | 6 |
| 75° | 2 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P244371

CATALOG NUMBER: LSR8B30D010 EC8B30930 8LBN0H

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 3531.9 |
| 1° | 3512.4 |
| 2° | 3476.4 |
| 3° | 3425.7 |
| 4° | 3360.1 |
| 5° | 3282.0 |
| 6° | 3193.6 |
| 7° | 3093.6 |
| 8° | 2993.5 |
| 9° | 2892.7 |
| 10° | 2796.7 |
| 11° | 2702.8 |
| 12° | 2614.6 |
| 13° | 2532.6 |
| 14° | 2450.5 |
| 15° | 2373.9 |
| 16° | 2298.9 |
| 17° | 2224.6 |
| 18° | 2152.8 |
| 19° | 2080.1 |
| 20° | 2008.9 |
| 21° | 1937.9 |
| 22° | 1869.9 |
| 23° | 1802.7 |
| 24° | 1734.0 |
| 25° | 1665.1 |
| 26° | 1594.1 |
| 27° | 1516.7 |
| 28° | 1435.4 |
| 29° | 1346.3 |
| 30° | 1250.3 |
| 32.5° | 980.7 |
| 35° | 690.0 |
| 37.5° | 454.8 |
| 40° | 297.7 |
| 42.5° | 205.5 |
| 45° | 142.3 |
| 47.5° | 97.6 |
| 50° | 64.9 |
| 52.5° | 42.1 |
| 55° | 28.1 |
| 57.5° | 18.7 |
| 60° | 12.6 |
| 62.5° | 8.6 |
| 65° | 6.3 |



TEST NUMBER: P244371

CATALOG NUMBER: LSR8B30D010 EC8B30930 8LBN0H

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|-----|
| 67.5° | 3.9 |
| 70° | 2.4 |
| 72.5° | 1.6 |
| 75° | 1.6 |
| 77.5° | 0.8 |
| 80° | 0.8 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)