

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243987

Luminaire Tested: **LSR8B30D010 EC8B30935 8LBM0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243987
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-11)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30935 8LBM0LI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 3500 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2737.1 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.72
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243987

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243987

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	73	80	75	72		79	75	72		77	74	71	70
7	86	78	72	69	85	77	72	68	76	71	68		75	71	68		74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	60	59
10	76	67	62	58	75	67	61	58	66	61	58		65	61	58		64	60	58	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147234
5°	140903
10°	125442
15°	100775
20°	78927
25°	63727
30°	49383
35°	28128
40°	10611
45°	4575
50°	1842
55°	688
60°	370
65°	248
70°	153
75°	107
80°	0
85°	0



TEST NUMBER: P243987

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	417.8	15.3
10°-20°	876.6	32.0
20°-30°	857.8	31.3
30°-40°	474.6	17.3
40°-50°	91.9	3.4
50°-60°	14.1	0.5
60°-70°	3.5	0.1
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2152.1	78.6
0°-40°	2626.7	96.0
0°-60°	2732.7	99.8
0°-90°	2737.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2737.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4775	
5°	4552	418
15°	3157	877
25°	1873	858
35°	747	475
45°	105	92
55°	13	14
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P243987

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4774.7
2.5°	4709.0
5°	4552.0
7.5°	4332.0
10°	4006.2
12.5°	3594.2
15°	3156.7
17.5°	2746.4
20°	2405.2
22.5°	2122.9
25°	1873.0
27.5°	1637.6
30°	1386.9
32.5°	1092.6
35°	747.2
37.5°	449.5
40°	263.6
42.5°	164.6
45°	104.9
47.5°	65.7
50°	38.4
52.5°	21.3
55°	12.8
57.5°	7.7
60°	6.0
62.5°	4.3
65°	3.4
67.5°	2.6
70°	1.7
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)