

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251118

Luminaire Tested: **LSR8B60D010 EC8B60935 8LBW0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251118
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P200903)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B60935 8LBW0WH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 3500 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5492.0 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.11
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251118

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBW0WH

Luminous Intensity Polar Plot





TEST NUMBER: P251118

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBW0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78	75	72	70
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73	69	66	64
6	83	73	67	62	82	73	66	62	71	65	61		69	64	61		68	64	60	59
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64	59	55	54
8	74	63	57	52	73	63	56	52	62	56	52		61	55	51		59	55	51	50
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	55	49	45	65	55	49	44	54	48	44		53	48	44		52	48	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	110943
5°	114344
10°	121876
15°	125634
20°	125627
25°	121789
30°	109003
35°	86819
40°	63436
45°	40517
50°	21914
55°	11263
60°	4897
65°	1007
70°	694
75°	0
80°	231
85°	0



TEST NUMBER: P251118

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBW0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	359.5	6.5
10°-20°	1106.3	20.1
20°-30°	1623.1	29.6
30°-40°	1433.8	26.1
40°-50°	734.4	13.4
50°-60°	205.3	3.7
60°-70°	26.2	0.5
70°-80°	2.7	0.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3088.9	56.2
0°-40°	4522.8	82.4
0°-60°	5462.5	99.5
0°-90°	5492.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5492.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3598	
5°	3694	360
15°	3935	1106
25°	3580	1623
35°	2306	1434
45°	929	734
55°	210	205
65°	14	26
75°	0	3
85°	0	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251118

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBW0WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3597.8
2.5°	3611.6
5°	3694.0
7.5°	3806.8
10°	3892.3
12.5°	3934.0
15°	3935.4
17.5°	3895.8
20°	3828.3
22.5°	3721.5
25°	3579.5
27.5°	3367.5
30°	3061.3
32.5°	2698.3
35°	2306.3
37.5°	1924.3
40°	1575.9
42.5°	1247.0
45°	929.1
47.5°	663.1
50°	456.8
52.5°	319.2
55°	209.5
57.5°	133.1
60°	79.4
62.5°	41.2
65°	13.8
67.5°	9.0
70°	7.7
72.5°	4.5
75°	0.0
77.5°	1.3
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251118

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBW0WH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)