

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246651

Luminaire Tested: **LSR8B30D010 EC8B30935 8LBN0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246651
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30935 8LBN0MW
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 3500 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2429.0 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246651

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBN0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246651

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBN0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78549
5°	77986
10°	71066
15°	60914
20°	53984
25°	48175
30°	38904
35°	26995
40°	17128
45°	12721
50°	10861
55°	9521
60°	8517
65°	7610
70°	6564
75°	6029
80°	5629
85°	4953



TEST NUMBER: P246651

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBN0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.4	9.6
10°-20°	537.5	22.1
20°-30°	639.2	26.3
30°-40°	451.9	18.6
40°-50°	233.2	9.6
50°-60°	159.9	6.6
60°-70°	103.8	4.3
70°-80°	54.4	2.2
80°-90°	16.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1409.0	58.0
0°-40°	1860.9	76.6
0°-60°	2254.1	92.8
0°-90°	2429.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2429.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2547	
5°	2519	232
15°	1908	537
25°	1416	639
35°	717	452
45°	292	233
55°	177	160
65°	104	104
75°	51	54
85°	14	16
90°	0	1
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P246651

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBN0MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2547.3
2.5°	2547.3
5°	2519.4
7.5°	2426.7
10°	2269.6
12.5°	2082.2
15°	1908.1
17.5°	1764.8
20°	1645.1
22.5°	1531.9
25°	1415.9
27.5°	1270.3
30°	1092.6
32.5°	901.5
35°	717.1
37.5°	552.5
40°	425.5
42.5°	342.4
45°	291.7
47.5°	255.0
50°	226.4
52.5°	201.3
55°	177.1
57.5°	155.8
60°	138.1
62.5°	119.7
65°	104.3
67.5°	90.4
70°	72.8
72.5°	62.5
75°	50.6
77.5°	41.1
80°	31.7
82.5°	23.6
85°	14.0
87.5°	8.1
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246651

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBN0MW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)