

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251186

Luminaire Tested: **LSR8B60D010 EC8B609730 8LBS0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251186  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B60D010 EC8B609730 8LBS0WH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 3000 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5755.0 lumens  
Efficiency: N/A  
Efficacy: 96.7 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251186

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBS0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P251186

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBS0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	100517
5°	100901
10°	102171
15°	104168
20°	105655
25°	106091
30°	102843
35°	93866
40°	81196
45°	63922
50°	41233
55°	20236
60°	8320
65°	3648
70°	1055
75°	393
80°	302
85°	0



TEST NUMBER: P251186

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBS0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	311.3	5.4
10°-20°	922.1	16.0
20°-30°	1427.7	24.8
30°-40°	1546.7	26.9
40°-50°	1113.0	19.3
50°-60°	372.4	6.5
60°-70°	56.3	1.0
70°-80°	4.8	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2661.2	46.2
0°-40°	4207.8	73.1
0°-60°	5693.2	98.9
0°-90°	5755.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5755.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3260	
5°	3260	311
15°	3263	922
25°	3118	1428
35°	2494	1547
45°	1466	1113
55°	376	372
65°	50	56
75°	3	5
85°	0	1
90°	0	



TEST NUMBER: P251186

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBS0WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3259.7
2.5°	3259.7
5°	3259.7
7.5°	3261.4
10°	3263.0
12.5°	3266.4
15°	3263.0
17.5°	3249.7
20°	3219.7
22.5°	3174.8
25°	3118.1
27.5°	3028.2
30°	2888.3
32.5°	2705.0
35°	2493.5
37.5°	2265.3
40°	2017.1
42.5°	1750.6
45°	1465.8
47.5°	1157.6
50°	859.5
52.5°	589.6
55°	376.4
57.5°	224.9
60°	134.9
62.5°	81.6
65°	50.0
67.5°	25.0
70°	11.7
72.5°	5.0
75°	3.3
77.5°	3.3
80°	1.7
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)