

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244014

Luminaire Tested: **LSR8B10D010 EC8B10827 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244014
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B10D010 EC8B10827 8LBS0LI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 2700 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1195.0 lumens
Efficiency: N/A
Efficacy: 117.2 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244014

CATALOG NUMBER: LSR8B10D010 EC8B10827 8LBSOLI

Luminous Intensity Polar Plot





TEST NUMBER: P244014

CATALOG NUMBER: LSR8B10D010 EC8B10827 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88		91	88	86		88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78		84	80	77		82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63		71	66	62		69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56		66	60	56		64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51		61	55	51		59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47		56	51	46		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39		49	43	39		48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	20546
5°	20634
10°	20970
15°	21501
20°	21875
25°	21901
30°	21222
35°	19432
40°	16887
45°	13362
50°	8664
55°	4328
60°	1819
65°	803
70°	243
75°	119
80°	124
85°	106



TEST NUMBER: P244014

CATALOG NUMBER: LSR8B10D010 EC8B10827 8LBS0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.7	5.3
10°-20°	190.3	15.9
20°-30°	294.8	24.7
30°-40°	320.2	26.8
40°-50°	232.6	19.5
50°-60°	79.1	6.6
60°-70°	12.6	1.1
70°-80°	1.3	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	548.9	45.9
0°-40°	869.0	72.7
0°-60°	1180.8	98.8
0°-90°	1195.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1195.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	666	
5°	667	64
15°	674	190
25°	644	295
35°	516	320
45°	306	233
55°	80	79
65°	11	13
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P244014

CATALOG NUMBER: LSR8B10D010 EC8B10827 8LBSOLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	666.3
2.5°	666.3
5°	666.6
7.5°	667.6
10°	669.7
12.5°	672.1
15°	673.5
17.5°	672.1
20°	666.6
22.5°	656.7
25°	643.7
27.5°	624.1
30°	596.0
32.5°	558.7
35°	516.2
37.5°	469.9
40°	419.5
42.5°	365.0
45°	306.4
47.5°	243.3
50°	180.6
52.5°	123.7
55°	80.5
57.5°	49.0
60°	29.5
62.5°	18.2
65°	11.0
67.5°	6.2
70°	2.7
72.5°	1.7
75°	1.0
77.5°	0.7
80°	0.7
82.5°	0.3
85°	0.3
87.5°	0.0
90°	0.0

(END OF REPORT)