

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245532

Luminaire Tested: **LSR8B10D010 EC8B10830 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245532
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B10D010 EC8B10830 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 978.0 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245532

CATALOG NUMBER: LSR8B10D010 EC8B10830 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245532

CATALOG NUMBER: LSR8B10D010 EC8B10830 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66	74	70	66	73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51	60	55	51	59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	23482
5°	22928
10°	22210
15°	21887
20°	21629
25°	21166
30°	19826
35°	16187
40°	9665
45°	5804
50°	4183
55°	2849
60°	1782
65°	876
70°	225
75°	83
80°	71
85°	0



TEST NUMBER: P245532

CATALOG NUMBER: LSR8B10D010 EC8B10830 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.7	7.1
10°-20°	193.5	19.8
20°-30°	284.1	29.1
30°-40°	257.6	26.3
40°-50°	110.2	11.3
50°-60°	48.8	5.0
60°-70°	13.0	1.3
70°-80°	1.0	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	547.3	56.0
0°-40°	804.9	82.3
0°-60°	963.9	98.6
0°-90°	978.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	978.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	762	
5°	741	70
15°	686	193
25°	622	284
35°	430	258
45°	133	110
55°	53	49
65°	12	13
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P245532

CATALOG NUMBER: LSR8B10D010 EC8B10830 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	761.5
2.5°	755.5
5°	740.7
7.5°	723.7
10°	709.3
12.5°	697.3
15°	685.6
17.5°	673.3
20°	659.1
22.5°	642.5
25°	622.1
27.5°	594.5
30°	556.8
32.5°	503.8
35°	430.0
37.5°	333.3
40°	240.1
42.5°	173.3
45°	133.1
47.5°	107.3
50°	87.2
52.5°	69.2
55°	53.0
57.5°	39.5
60°	28.9
62.5°	20.1
65°	12.0
67.5°	5.3
70°	2.5
72.5°	1.4
75°	0.7
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)