

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244071

Luminaire Tested: **LSR8B30D010 EC8B30950 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244071
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30950 8LBS0LI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3216.0 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244071

CATALOG NUMBER: LSR8B30D010 EC8B30950 8LBSOLI

Luminous Intensity Polar Plot





TEST NUMBER: P244071

CATALOG NUMBER: LSR8B30D010 EC8B30950 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88		91	88	86		88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78		84	80	77		82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63		71	66	62		69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56		66	60	56		64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51		61	55	51		59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47		56	51	46		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39		49	43	39		48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55293
5°	55532
10°	56434
15°	57862
20°	58871
25°	58937
30°	57113
35°	52292
40°	45447
45°	35960
50°	23320
55°	11655
60°	4891
65°	2152
70°	667
75°	334
80°	320
85°	318



TEST NUMBER: P244071

CATALOG NUMBER: LSR8B30D010 EC8B30950 8LBS0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.5	5.3
10°-20°	512.2	15.9
20°-30°	793.4	24.7
30°-40°	861.7	26.8
40°-50°	626.1	19.5
50°-60°	212.8	6.6
60°-70°	33.9	1.1
70°-80°	3.6	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1477.1	45.9
0°-40°	2338.8	72.7
0°-60°	3177.7	98.8
0°-90°	3216.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3216.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1793	
5°	1794	172
15°	1812	512
25°	1732	793
35°	1389	862
45°	825	626
55°	217	213
65°	30	34
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P244071

CATALOG NUMBER: LSR8B30D010 EC8B30950 8LBS0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1793.1
2.5°	1793.1
5°	1794.0
7.5°	1796.8
10°	1802.3
12.5°	1808.8
15°	1812.5
17.5°	1808.8
20°	1794.0
22.5°	1767.3
25°	1732.2
27.5°	1679.6
30°	1604.0
32.5°	1503.5
35°	1389.1
37.5°	1264.6
40°	1129.0
42.5°	982.3
45°	824.6
47.5°	654.9
50°	486.1
52.5°	333.0
55°	216.8
57.5°	131.9
60°	79.3
62.5°	48.9
65°	29.5
67.5°	16.6
70°	7.4
72.5°	4.6
75°	2.8
77.5°	1.8
80°	1.8
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)