

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245790

Luminaire Tested: **LSR8B10D010 EC8B10940 8LBSOGPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245790
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B10D010 EC8B10940 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 4000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1003.0 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245790

CATALOG NUMBER: LSR8B10D010 EC8B10940 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245790

CATALOG NUMBER: LSR8B10D010 EC8B10940 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61		70	65	61		68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50		59	54	50		58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	17752
5°	17700
10°	17525
15°	17344
20°	17162
25°	16883
30°	16422
35°	15671
40°	14572
45°	12302
50°	8352
55°	4365
60°	1955
65°	956
70°	388
75°	238
80°	178
85°	106



TEST NUMBER: P245790

CATALOG NUMBER: LSR8B10D010 EC8B10940 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	5.4
10°-20°	153.2	15.3
20°-30°	228.1	22.7
30°-40°	259.3	25.9
40°-50°	212.0	21.1
50°-60°	79.0	7.9
60°-70°	14.4	1.4
70°-80°	2.2	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	435.6	43.4
0°-40°	694.9	69.3
0°-60°	986.0	98.3
0°-90°	1003.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1003.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	576	
5°	572	54
15°	543	153
25°	496	228
35°	416	259
45°	282	212
55°	81	79
65°	13	14
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P245790

CATALOG NUMBER: LSR8B10D010 EC8B10940 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	575.7
2.5°	574.7
5°	571.8
7.5°	566.6
10°	559.7
12.5°	551.8
15°	543.3
17.5°	533.5
20°	523.0
22.5°	510.6
25°	496.2
27.5°	479.8
30°	461.2
32.5°	439.9
35°	416.3
37.5°	391.1
40°	362.0
42.5°	326.0
45°	282.1
47.5°	229.4
50°	174.1
52.5°	122.7
55°	81.2
57.5°	51.1
60°	31.7
62.5°	20.3
65°	13.1
67.5°	7.5
70°	4.3
72.5°	2.6
75°	2.0
77.5°	1.3
80°	1.0
82.5°	0.3
85°	0.3
87.5°	0.0
90°	0.0

(END OF REPORT)