

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244684

Luminaire Tested: **LSR8B40D010 EC8B40840 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244684
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B40D010 EC8B40840 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 4000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4252.0 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244684

CATALOG NUMBER: LSR8B40D010 EC8B40840 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244684

CATALOG NUMBER: LSR8B40D010 EC8B40840 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	95022
5°	93110
10°	90160
15°	88947
20°	88414
25°	87299
30°	82604
35°	68132
40°	42540
45°	27356
50°	21214
55°	16333
60°	12372
65°	8041
70°	3435
75°	1680
80°	746
85°	495



TEST NUMBER: P244684

CATALOG NUMBER: LSR8B40D010 EC8B40840 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.9	6.7
10°-20°	787.1	18.5
20°-30°	1172.4	27.6
30°-40°	1088.8	25.6
40°-50°	514.3	12.1
50°-60°	276.3	6.5
60°-70°	110.9	2.6
70°-80°	17.4	0.4
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2242.5	52.7
0°-40°	3331.3	78.3
0°-60°	4121.9	96.9
0°-90°	4252.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4252.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3082	
5°	3008	283
15°	2786	787
25°	2566	1172
35°	1810	1089
45°	627	514
55°	304	276
65°	110	111
75°	14	17
85°	1	2
90°	0	



TEST NUMBER: P244684

CATALOG NUMBER: LSR8B40D010 EC8B40840 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3081.5
2.5°	3060.3
5°	3008.0
7.5°	2941.6
10°	2879.4
12.5°	2828.5
15°	2786.2
17.5°	2742.4
20°	2694.3
22.5°	2639.2
25°	2565.8
27.5°	2462.6
30°	2319.9
32.5°	2110.8
35°	1809.9
37.5°	1425.6
40°	1056.8
42.5°	787.0
45°	627.3
47.5°	524.2
50°	442.2
52.5°	368.8
55°	303.8
57.5°	247.3
60°	200.6
62.5°	156.8
65°	110.2
67.5°	65.0
70°	38.1
72.5°	22.6
75°	14.1
77.5°	8.5
80°	4.2
82.5°	2.8
85°	1.4
87.5°	0.0
90°	0.0

(END OF REPORT)