

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244042

Luminaire Tested: **LSR8B40D010 EC8B40850 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244042
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B40D010 EC8B40850 8LBS0LI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5024.0 lumens
Efficiency: N/A
Efficacy: 122.8 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244042

CATALOG NUMBER: LSR8B40D010 EC8B40850 8LBSOLI

Luminous Intensity Polar Plot





TEST NUMBER: P244042

CATALOG NUMBER: LSR8B40D010 EC8B40850 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88	91	88	86	88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63	71	66	62	69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47	56	51	46	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39	49	43	39	48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86379
5°	86752
10°	88162
15°	90390
20°	91968
25°	92073
30°	89223
35°	81688
40°	70996
45°	56177
50°	36431
55°	18204
60°	7641
65°	3364
70°	1037
75°	512
80°	515
85°	495



TEST NUMBER: P244042

CATALOG NUMBER: LSR8B40D010 EC8B40850 8LBS0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.9	5.3
10°-20°	800.1	15.9
20°-30°	1239.5	24.7
30°-40°	1346.1	26.8
40°-50°	978.2	19.5
50°-60°	332.5	6.6
60°-70°	52.9	1.1
70°-80°	5.7	0.1
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2307.5	45.9
0°-40°	3653.6	72.7
0°-60°	4964.2	98.8
0°-90°	5024.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5024.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2801	
5°	2803	268
15°	2831	800
25°	2706	1239
35°	2170	1346
45°	1288	978
55°	339	332
65°	46	53
75°	4	6
85°	1	1
90°	0	



TEST NUMBER: P244042

CATALOG NUMBER: LSR8B40D010 EC8B40850 8LBS0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2801.2
2.5°	2801.2
5°	2802.6
7.5°	2806.9
10°	2815.6
12.5°	2825.7
15°	2831.4
17.5°	2825.7
20°	2802.6
22.5°	2760.8
25°	2706.1
27.5°	2623.9
30°	2505.8
32.5°	2348.7
35°	2170.0
37.5°	1975.5
40°	1763.7
42.5°	1534.6
45°	1288.2
47.5°	1023.1
50°	759.4
52.5°	520.2
55°	338.6
57.5°	206.1
60°	123.9
62.5°	76.4
65°	46.1
67.5°	25.9
70°	11.5
72.5°	7.2
75°	4.3
77.5°	2.9
80°	2.9
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0

(END OF REPORT)