

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247728

Luminaire Tested: **LSR8B100D010 EC8B100835 8LBS0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-88)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B100D010 EC8B100835 8LBS0MW
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3500 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12040.0 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.24
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 106.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247728

CATALOG NUMBER: LSR8B100D010 EC8B100835 8LBS0MW

Luminous Intensity Polar Plot





TEST NUMBER: P247728

CATALOG NUMBER: LSR8B100D010 EC8B100835 8LBS0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61
5	83	72	64	59	81	71	64	58	69	62	58	67	61	57	65	60	57	55
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49
7	72	60	52	47	70	59	52	47	58	51	47	57	51	46	55	50	46	44
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37
10	60	47	40	36	58	47	40	35	46	40	35	45	39	35	44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	197149
5°	196655
10°	195183
15°	193150
20°	189587
25°	185387
30°	179155
35°	171014
40°	159699
45°	136797
50°	102858
55°	69723
60°	45360
65°	33279
70°	27183
75°	30810
80°	32302
85°	26217



TEST NUMBER: P247728

CATALOG NUMBER: LSR8B100D010 EC8B100835 8LBS0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	602.9	5.0
10°-20°	1702.0	14.1
20°-30°	2503.9	20.8
30°-40°	2828.2	23.5
40°-50°	2381.9	19.8
50°-60°	1201.7	10.0
60°-70°	470.8	3.9
70°-80°	265.8	2.2
80°-90°	82.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4808.9	39.9
0°-40°	7637.1	63.4
0°-60°	11220.7	93.2
0°-90°	12040.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12040.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6393	
5°	6353	603
15°	6050	1702
25°	5449	2504
35°	4543	2828
45°	3137	2382
55°	1297	1202
65°	456	471
75°	259	266
85°	74	83
90°	0	



TEST NUMBER: P247728

CATALOG NUMBER: LSR8B100D010 EC8B100835 8LBS0MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6393.4
2.5°	6386.9
5°	6353.1
7.5°	6308.9
10°	6233.5
12.5°	6140.0
15°	6050.3
17.5°	5913.9
20°	5777.4
22.5°	5629.3
25°	5448.7
27.5°	5244.6
30°	5031.5
32.5°	4792.4
35°	4542.9
37.5°	4257.0
40°	3967.3
42.5°	3572.2
45°	3136.9
47.5°	2637.9
50°	2144.1
52.5°	1698.4
55°	1296.9
57.5°	977.2
60°	735.5
62.5°	561.4
65°	456.1
67.5°	371.6
70°	301.5
72.5°	291.1
75°	258.6
77.5°	215.7
80°	181.9
82.5°	115.7
85°	74.1
87.5°	23.4
90°	0.0

(END OF REPORT)