

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245806

Luminaire Tested: **LSR8B40D010 EC8B40927 8LBS0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245806  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B40D010 EC8B40927 8LBS0GPH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 2700 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3414.4 lumens  
Efficiency: N/A  
Efficacy: 83.5 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 40.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245806

CATALOG NUMBER: LSR8B40D010 EC8B40927 8LBS0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P245806

CATALOG NUMBER: LSR8B40D010 EC8B40927 8LBS0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61		70	65	61		68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50		59	54	50		58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38		48	42	38		47	42	38	36

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P245806

CATALOG NUMBER: LSR8B40D010 EC8B40927 8LBS0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	184.5	5.4
10°-20°	521.7	15.3
20°-30°	776.6	22.7
30°-40°	882.8	25.9
40°-50°	721.9	21.1
50°-60°	269.1	7.9
60°-70°	49.2	1.4
70°-80°	7.6	0.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1482.7	43.4
0°-40°	2365.6	69.3
0°-60°	3356.5	98.3
0°-90°	3414.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3414.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1960	
5°	1946	184
15°	1850	522
25°	1689	777
35°	1417	883
45°	960	722
55°	276	269
65°	45	49
75°	7	8
85°	1	1
90°	0	



TEST NUMBER: P245806

CATALOG NUMBER: LSR8B40D010 EC8B40927 8LBS0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1959.9
2.5°	1956.5
5°	1946.5
7.5°	1928.7
10°	1905.3
12.5°	1878.5
15°	1849.5
17.5°	1816.1
20°	1780.4
22.5°	1738.1
25°	1689.1
27.5°	1633.4
30°	1569.9
32.5°	1497.5
35°	1417.3
37.5°	1331.4
40°	1232.3
42.5°	1109.7
45°	960.4
47.5°	781.1
50°	592.8
52.5°	417.8
55°	276.3
57.5°	173.8
60°	108.1
62.5°	69.1
65°	44.6
67.5°	25.6
70°	14.5
72.5°	8.9
75°	6.6
77.5°	4.5
80°	3.4
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0

(END OF REPORT)