

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247012

Luminaire Tested: **LSR8B100D010 EC8B100840 8LBNOLI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247012  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-80)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B100D010 EC8B100840 8LBN0LI  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 4000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10287.0 lumens  
Efficiency: N/A  
Efficacy: 96.8 lumens/watt  
Spacing Criteria (0/90/45): 0.47 / 0.47 / 0.56  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 106.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P247012

CATALOG NUMBER: LSR8B100D010 EC8B100840 8LBN0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P247012

CATALOG NUMBER: LSR8B100D010 EC8B100840 8LBN0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	107	104	100	98	100	98	96		98	95	94		95	93	92	90
3	105	100	95	92	103	98	94	91	96	92	90		93	91	88		91	89	87	85
4	101	94	90	86	99	93	89	85	91	87	84		89	86	83		87	85	83	81
5	97	90	85	81	95	89	84	80	87	83	80		85	82	79		84	81	78	77
6	93	85	80	76	91	84	80	76	83	79	76		82	78	75		80	77	75	73
7	89	81	76	72	88	81	76	72	79	75	72		78	74	72		77	74	71	70
8	86	78	72	69	85	77	72	69	76	72	69		75	71	68		74	71	68	67
9	82	74	69	66	81	74	69	66	73	69	65		72	68	65		71	68	65	64
10	79	71	66	63	79	71	66	63	70	66	63		69	65	62		69	65	62	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	805845
5°	762969
10°	574610
15°	399393
20°	297730
25°	224100
30°	149851
35°	78435
40°	30295
45°	11203
50°	2850
55°	554
60°	80
65°	285
70°	352
75°	0
80°	0
85°	460



TEST NUMBER: P247012

CATALOG NUMBER: LSR8B100D010 EC8B100840 8LBN0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2143.3	20.8
10°-20°	3544.5	34.5
20°-30°	2988.2	29.0
30°-40°	1355.9	13.2
40°-50°	236.7	2.3
50°-60°	12.9	0.1
60°-70°	1.9	0.0
70°-80°	2.2	0.0
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8675.9	84.3
0°-40°	10031.9	97.5
0°-60°	10281.4	99.9
0°-90°	10287.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10287.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	26133	
5°	24648	###
15°	12511	3544
25°	6586	2988
35°	2084	1356
45°	257	237
55°	10	13
65°	4	2
75°	0	2
85°	1	1
90°	0	



TEST NUMBER: P247012

CATALOG NUMBER: LSR8B100D010 EC8B100840 8LBN0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	26133.0
2.5°	25901.9
5°	24648.4
7.5°	21918.0
10°	18351.1
12.5°	15053.9
15°	12510.7
17.5°	10600.1
20°	9072.9
22.5°	7729.0
25°	6586.5
27.5°	5424.6
30°	4208.5
32.5°	3063.5
35°	2083.6
37.5°	1279.3
40°	752.6
42.5°	441.5
45°	256.9
47.5°	153.6
50°	59.4
52.5°	9.0
55°	10.3
57.5°	9.0
60°	1.3
62.5°	1.3
65°	3.9
67.5°	0.0
70°	3.9
72.5°	6.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	1.3
87.5°	3.9
90°	0.0

(END OF REPORT)