

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244948

Luminaire Tested: **LSR8B40D010 EC8B40930 8LBS0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244948
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B40D010 EC8B40930 8LBS0WMH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3905.6 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244948

CATALOG NUMBER: LSR8B40D010 EC8B40930 8LBS0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244948

CATALOG NUMBER: LSR8B40D010 EC8B40930 8LBS0W/MH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86		90	87	85		88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76		83	79	75		80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68		76	71	67		74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61		70	64	60		68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55		64	58	54		63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49		59	53	49		58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45		55	49	45		54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41		51	45	41		50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38		47	42	38		46	41	37	36

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244948

CATALOG NUMBER: LSR8B40D010 EC8B40930 8LBS0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.5	5.3
10°-20°	590.1	15.1
20°-30°	878.5	22.5
30°-40°	997.9	25.6
40°-50°	815.7	20.9
50°-60°	319.7	8.2
60°-70°	74.5	1.9
70°-80°	18.0	0.5
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1677.0	42.9
0°-40°	2674.9	68.5
0°-60°	3810.3	97.6
0°-90°	3905.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3905.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2214	
5°	2199	208
15°	2092	590
25°	1911	878
35°	1604	998
45°	1083	816
55°	332	320
65°	69	74
75°	16	18
85°	2	3
90°	0	



TEST NUMBER: P244948

CATALOG NUMBER: LSR8B40D010 EC8B40930 8LBS0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2214.4
2.5°	2210.8
5°	2199.2
7.5°	2179.1
10°	2154.4
12.5°	2124.0
15°	2092.2
17.5°	2054.7
20°	2013.5
22.5°	1965.3
25°	1911.3
27.5°	1847.9
30°	1776.2
32.5°	1695.2
35°	1603.5
37.5°	1502.5
40°	1389.7
42.5°	1253.5
45°	1083.1
47.5°	883.5
50°	675.5
52.5°	485.2
55°	332.5
57.5°	217.4
60°	145.6
62.5°	99.9
65°	69.3
67.5°	45.8
70°	30.5
72.5°	21.2
75°	16.5
77.5°	11.8
80°	7.1
82.5°	3.5
85°	2.4
87.5°	1.1
90°	0.0

(END OF REPORT)