

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245716

Luminaire Tested: **LSR8B40D010 EC8B40935 8LBM0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245716  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201629)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B40D010 EC8B40935 8LBM0GPH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 3500 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3304.0 lumens  
Efficiency: N/A  
Efficacy: 80.8 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245716

CATALOG NUMBER: LSR8B40D010 EC8B40935 8LBM0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P245716

CATALOG NUMBER: LSR8B40D010 EC8B40935 8LBM0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	129235
5°	125955
10°	112939
15°	100567
20°	91761
25°	83332
30°	68340
35°	45000
40°	22425
45°	8338
50°	2538
55°	285
60°	173
65°	0
70°	117
75°	488
80°	0
85°	460



TEST NUMBER: P245716

CATALOG NUMBER: LSR8B40D010 EC8B40935 8LBM0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	373.1	11.3
10°-20°	887.1	26.8
20°-30°	1105.0	33.4
30°-40°	745.6	22.6
40°-50°	176.2	5.3
50°-60°	12.8	0.4
60°-70°	2.2	0.1
70°-80°	1.6	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2365.2	71.6
0°-40°	3110.8	94.2
0°-60°	3299.8	99.9
0°-90°	3304.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3304.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4191	
5°	4069	373
15°	3150	887
25°	2449	1105
35°	1195	746
45°	191	176
55°	5	13
65°	0	2
75°	4	2
85°	1	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P245716

CATALOG NUMBER: LSR8B40D010 EC8B40935 8LBM0GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4191.0
2.5°	4184.4
5°	4069.1
7.5°	3861.7
10°	3606.9
12.5°	3364.3
15°	3150.2
17.5°	2965.6
20°	2796.3
22.5°	2632.3
25°	2449.2
27.5°	2210.7
30°	1919.3
32.5°	1566.9
35°	1195.4
37.5°	855.4
40°	557.1
42.5°	333.4
45°	191.2
47.5°	107.1
50°	52.9
52.5°	24.4
55°	5.3
57.5°	1.3
60°	2.8
62.5°	4.1
65°	0.0
67.5°	2.8
70°	1.3
72.5°	1.3
75°	4.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	1.3
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245716

CATALOG NUMBER: LSR8B40D010 EC8B40935 8LBM0GPH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)