

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245590

Luminaire Tested: **LSR8B40D010 EC8B409727 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245590
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B40D010 EC8B409727 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 2700 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2744.0 lumens
Efficiency: N/A
Efficacy: 67.1 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245590

CATALOG NUMBER: LSR8B40D010 EC8B409727 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245590

CATALOG NUMBER: LSR8B40D010 EC8B409727 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66	74	70	66	73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51	60	55	51	59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P245590

CATALOG NUMBER: LSR8B40D010 EC8B409727 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.5	7.1
10°-20°	542.9	19.8
20°-30°	797.2	29.1
30°-40°	722.7	26.3
40°-50°	309.4	11.3
50°-60°	136.9	5.0
60°-70°	36.5	1.3
70°-80°	2.9	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1535.6	56.0
0°-40°	2258.3	82.3
0°-60°	2704.5	98.6
0°-90°	2744.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2744.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2137	
5°	2078	196
15°	1924	543
25°	1745	797
35°	1206	723
45°	373	309
55°	149	137
65°	34	37
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P245590

CATALOG NUMBER: LSR8B40D010 EC8B409727 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2136.6
2.5°	2119.8
5°	2078.2
7.5°	2030.6
10°	1990.0
12.5°	1956.3
15°	1923.7
17.5°	1889.0
20°	1849.4
22.5°	1802.8
25°	1745.4
27.5°	1668.1
30°	1562.1
32.5°	1413.5
35°	1206.5
37.5°	935.1
40°	673.6
42.5°	486.4
45°	373.4
47.5°	301.1
50°	244.7
52.5°	194.1
55°	148.6
57.5°	110.9
60°	81.2
62.5°	56.5
65°	33.7
67.5°	14.9
70°	6.9
72.5°	4.0
75°	2.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)