

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246629

Luminaire Tested: **LSR8B50D010 EC8B50840 8LBN0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246629
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B50D010 EC8B50840 8LBN0MW
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 4000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5037.0 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246629

CATALOG NUMBER: LSR8B50D010 EC8B50840 8LBN0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246629

CATALOG NUMBER: LSR8B50D010 EC8B50840 8LBN0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98		98	97	95		95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71		78	74	70		76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65		73	68	64		71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55		64	59	55		63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53	48	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	162884
5°	161717
10°	147370
15°	126317
20°	111946
25°	99898
30°	80678
35°	55977
40°	35516
45°	26384
50°	22518
55°	19741
60°	17669
65°	15782
70°	13605
75°	12510
80°	11649
85°	10296



TEST NUMBER: P246629

CATALOG NUMBER: LSR8B50D010 EC8B50840 8LBN0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	481.9	9.6
10°-20°	1114.6	22.1
20°-30°	1325.5	26.3
30°-40°	937.0	18.6
40°-50°	483.7	9.6
50°-60°	331.6	6.6
60°-70°	215.2	4.3
70°-80°	112.9	2.2
80°-90°	34.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2921.9	58.0
0°-40°	3858.9	76.6
0°-60°	4674.2	92.8
0°-90°	5037.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5037.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5282	
5°	5224	482
15°	3957	1115
25°	2936	1325
35°	1487	937
45°	605	484
55°	367	332
65°	216	215
75°	105	113
85°	29	32
90°	0	2
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P246629

CATALOG NUMBER: LSR8B50D010 EC8B50840 8LBN0MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5282.2
2.5°	5282.2
5°	5224.4
7.5°	5032.3
10°	4706.5
12.5°	4317.8
15°	3956.8
17.5°	3659.7
20°	3411.4
22.5°	3176.7
25°	2936.1
27.5°	2634.1
30°	2265.8
32.5°	1869.5
35°	1487.0
37.5°	1145.7
40°	882.3
42.5°	710.0
45°	605.0
47.5°	528.7
50°	469.4
52.5°	417.4
55°	367.2
57.5°	323.0
60°	286.5
62.5°	248.2
65°	216.3
67.5°	187.4
70°	150.9
72.5°	129.6
75°	105.0
77.5°	85.2
80°	65.6
82.5°	48.9
85°	29.1
87.5°	16.8
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246629

CATALOG NUMBER: LSR8B50D010 EC8B50840 8LBN0MW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)