

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244757

Luminaire Tested: **LSR8B50D010 EC8B50840 8LBN0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244757  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201884)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B50D010 EC8B50840 8LBN0WMH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 4000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4807.0 lumens  
Efficiency: N/A  
Efficacy: 90.7 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 53  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244757

CATALOG NUMBER: LSR8B50D010 EC8B50840 8LBN0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244757

CATALOG NUMBER: LSR8B50D010 EC8B50840 8LBN0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93		96	94	91		93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86		91	88	85		89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80		86	82	79		84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75		81	77	74		80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70		77	73	70		76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66		73	69	66		72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62		70	65	62		69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59		66	62	59		65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56		63	59	55		62	58	55	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	215873
5°	212862
10°	194764
15°	167218
20°	140811
25°	116315
30°	87265
35°	52013
40°	24772
45°	10793
50°	4869
55°	2140
60°	1270
65°	693
70°	721
75°	0
80°	284
85°	1168



TEST NUMBER: P244757

CATALOG NUMBER: LSR8B50D010 EC8B50840 8LBN0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	635.1	13.2
10°-20°	1459.5	30.4
20°-30°	1548.6	32.2
30°-40°	883.6	18.4
40°-50°	219.0	4.6
50°-60°	43.0	0.9
60°-70°	12.9	0.3
70°-80°	2.9	0.1
80°-90°	2.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3643.2	75.8
0°-40°	4526.8	94.2
0°-60°	4788.8	99.6
0°-90°	4807.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4807.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7001	
5°	6877	635
15°	5238	1460
25°	3419	1549
35°	1382	884
45°	248	219
55°	40	43
65°	10	13
75°	0	3
85°	3	2
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P244757

CATALOG NUMBER: LSR8B50D010 EC8B50840 8LBN0WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7000.6
2.5°	6997.3
5°	6876.7
7.5°	6611.7
10°	6220.1
12.5°	5747.2
15°	5238.0
17.5°	4752.7
20°	4291.0
22.5°	3847.0
25°	3418.6
27.5°	2958.5
30°	2450.8
32.5°	1905.1
35°	1381.7
37.5°	951.8
40°	615.4
42.5°	390.2
45°	247.5
47.5°	161.9
50°	101.5
52.5°	61.7
55°	39.8
57.5°	31.8
60°	20.6
62.5°	19.0
65°	9.5
67.5°	9.5
70°	8.0
72.5°	4.7
75°	0.0
77.5°	1.6
80°	1.6
82.5°	3.3
85°	3.3
87.5°	1.6
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P244757

CATALOG NUMBER: LSR8B50D010 EC8B50840 8LBN0WMH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)