

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250375

Luminaire Tested: **LSR8B120D010 EC8B120827 8LBN0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250375  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B120D010 EC8B120827 8LBN0B  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 2700 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6831.0 lumens  
Efficiency: N/A  
Efficacy: 57.7 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 118.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250375

CATALOG NUMBER: LSR8B120D010 EC8B120827 8LBN0B

### Luminous Intensity Polar Plot





TEST NUMBER: P250375

CATALOG NUMBER: LSR8B120D010 EC8B120827 8LBN0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 | 101 | 100 | 99  | 98  | 97  | 96  | 94  |
| 2   | 109 | 104 | 101 | 97  | 107 | 103 | 99  | 96  | 99  | 97  | 94  | 96  | 94  | 92  | 94  | 92  | 90  | 89  |
| 3   | 104 | 98  | 93  | 90  | 102 | 97  | 92  | 89  | 94  | 90  | 88  | 92  | 89  | 86  | 89  | 87  | 85  | 83  |
| 4   | 99  | 92  | 87  | 83  | 97  | 91  | 86  | 83  | 89  | 85  | 82  | 87  | 84  | 81  | 85  | 82  | 80  | 78  |
| 5   | 95  | 87  | 82  | 78  | 93  | 86  | 81  | 77  | 84  | 80  | 77  | 83  | 79  | 76  | 81  | 78  | 75  | 74  |
| 6   | 90  | 82  | 77  | 73  | 89  | 81  | 76  | 72  | 80  | 75  | 72  | 79  | 75  | 71  | 77  | 74  | 71  | 70  |
| 7   | 86  | 78  | 72  | 68  | 85  | 77  | 72  | 68  | 76  | 71  | 68  | 75  | 71  | 67  | 74  | 70  | 67  | 66  |
| 8   | 83  | 74  | 68  | 64  | 81  | 73  | 68  | 64  | 72  | 67  | 64  | 71  | 67  | 64  | 70  | 66  | 63  | 62  |
| 9   | 79  | 70  | 65  | 61  | 78  | 70  | 64  | 61  | 69  | 64  | 61  | 68  | 63  | 60  | 67  | 63  | 60  | 59  |
| 10  | 76  | 67  | 61  | 58  | 75  | 66  | 61  | 58  | 65  | 61  | 57  | 65  | 60  | 57  | 64  | 60  | 57  | 56  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 336588 |
| 5°  | 331209 |
| 10° | 294270 |
| 15° | 242748 |
| 20° | 204443 |
| 25° | 172438 |
| 30° | 129110 |
| 35° | 73067  |
| 40° | 28890  |
| 45° | 7758   |
| 50° | 1487   |
| 55° | 0      |
| 60° | 216    |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P250375

CATALOG NUMBER: LSR8B120D010 EC8B120827 8LBN0B

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 979.9  | 14.3      |
| 10°-20°   | 2129.7 | 31.2      |
| 20°-30°   | 2286.4 | 33.5      |
| 30°-40°   | 1235.7 | 18.1      |
| 40°-50°   | 192.8  | 2.8       |
| 50°-60°   | 5.3    | 0.1       |
| 60°-70°   | 1.3    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 5395.9 | 79.0      |
| 0°-40°    | 6631.6 | 97.1      |
| 0°-60°    | 6829.7 | 100.0     |
| 0°-90°    | 6831.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 6831.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 10915 |      |
| 5°  | 10700 | 980  |
| 15° | 7604  | 2130 |
| 25° | 5068  | 2286 |
| 35° | 1941  | 1236 |
| 45° | 178   | 193  |
| 55° | 0     | 5    |
| 65° | 0     | 1    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P250375

CATALOG NUMBER: LSR8B120D010 EC8B120827 8LBN0B

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 10915.3 |
| 1°    | 10936.0 |
| 2°    | 10925.7 |
| 3°    | 10888.3 |
| 4°    | 10816.4 |
| 5°    | 10700.0 |
| 6°    | 10539.7 |
| 7°    | 10324.1 |
| 8°    | 10054.1 |
| 9°    | 9743.5  |
| 10°   | 9398.0  |
| 11°   | 9035.7  |
| 12°   | 8659.8  |
| 13°   | 8284.2  |
| 14°   | 7935.3  |
| 15°   | 7603.9  |
| 16°   | 7299.7  |
| 17°   | 7005.8  |
| 18°   | 6732.3  |
| 19°   | 6476.3  |
| 20°   | 6230.1  |
| 21°   | 5990.8  |
| 22°   | 5765.1  |
| 23°   | 5539.9  |
| 24°   | 5304.0  |
| 25°   | 5068.1  |
| 26°   | 4828.8  |
| 27°   | 4555.5  |
| 28°   | 4254.6  |
| 29°   | 3947.4  |
| 30°   | 3626.0  |
| 31°   | 3280.9  |
| 32°   | 2935.4  |
| 33°   | 2593.8  |
| 34°   | 2248.7  |
| 35°   | 1941.0  |
| 37.5° | 1240.5  |
| 40°   | 717.7   |
| 42.5° | 382.9   |
| 45°   | 177.9   |
| 47.5° | 95.9    |
| 50°   | 31.0    |
| 52.5° | 3.5     |
| 55°   | 0.0     |
| 57.5° | 3.5     |



TEST NUMBER: P250375

CATALOG NUMBER: LSR8B120D010 EC8B120827 8LBN0B

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 60°   | 3.5 |
| 62.5° | 0.0 |
| 65°   | 0.0 |
| 67.5° | 3.5 |
| 70°   | 0.0 |
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)