

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251330

Luminaire Tested: **LSR8B60D010 EC8B60830 8LBW0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251330  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B60D010 EC8B60830 8LBW0B  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 3000 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3818.0 lumens  
Efficiency: N/A  
Efficacy: 64.2 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251330

CATALOG NUMBER: LSR8B60D010 EC8B60830 8LBW0B

### Luminous Intensity Polar Plot





TEST NUMBER: P251330

CATALOG NUMBER: LSR8B60D010 EC8B60830 8LBW0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101	101	101	99	98	98	97	96	95	95	93
2	107	102	98	95	105	101	97	94	97	94	92	92	94	92	90	90	92	90	88	88	86
3	102	95	90	86	100	94	89	85	91	87	84	84	89	85	82	82	86	84	81	81	80
4	96	88	83	78	94	87	82	78	85	80	77	77	83	79	76	76	81	78	75	75	74
5	91	82	76	72	89	81	76	71	80	75	71	71	78	74	70	70	76	73	70	70	68
6	86	77	71	66	85	76	70	66	74	69	65	65	73	68	65	65	72	68	65	65	63
7	82	72	66	61	80	71	65	61	70	64	61	61	69	64	60	60	67	63	60	60	58
8	77	67	61	57	76	67	61	57	66	60	56	56	65	60	56	56	64	59	56	56	54
9	73	63	57	53	72	63	57	53	62	56	52	52	61	56	52	52	60	55	52	52	51
10	70	59	53	49	68	59	53	49	58	53	49	49	57	52	49	49	57	52	49	49	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	107662
5°	104953
10°	102159
15°	100258
20°	97649
25°	94189
30°	86421
35°	66261
40°	31527
45°	12006
50°	5857
55°	2398
60°	598
65°	139
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P251330

CATALOG NUMBER: LSR8B60D010 EC8B60830 8LBW0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	319.6	8.4
10°-20°	883.8	23.1
20°-30°	1261.9	33.1
30°-40°	1045.8	27.4
40°-50°	257.9	6.8
50°-60°	46.4	1.2
60°-70°	2.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2465.3	64.6
0°-40°	3511.1	92.0
0°-60°	3815.4	99.9
0°-90°	3818.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3818.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3491	
5°	3391	320
15°	3140	884
25°	2768	1262
35°	1760	1046
45°	275	258
55°	45	46
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P251330

CATALOG NUMBER: LSR8B60D010 EC8B60830 8LBW0B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3491.4
2.5°	3462.3
5°	3390.6
7.5°	3320.8
10°	3262.6
12.5°	3206.4
15°	3140.5
17.5°	3063.0
20°	2975.7
22.5°	2876.9
25°	2768.3
27.5°	2621.0
30°	2427.1
32.5°	2153.8
35°	1760.2
37.5°	1271.7
40°	783.2
42.5°	455.6
45°	275.3
47.5°	182.2
50°	122.1
52.5°	79.5
55°	44.6
57.5°	21.3
60°	9.7
62.5°	3.9
65°	1.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)