

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251398

Luminaire Tested: **LSR8B60D010 EC8B60835 8LBS0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251398
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-17)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B60835 8LBS0B
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3500 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5684.0 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251398

CATALOG NUMBER: LSR8B60D010 EC8B60835 8LBS0B

Luminous Intensity Polar Plot





TEST NUMBER: P251398

CATALOG NUMBER: LSR8B60D010 EC8B60835 8LBS0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	94	90	103	98	93	89	94	90	87	91	88	85	88	86	84	82
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73
4	92	82	76	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59
6	80	69	62	56	78	68	61	56	67	60	56	65	60	55	64	59	55	53
7	75	63	56	51	73	63	56	51	61	55	51	60	54	50	59	54	50	48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	101535
5°	101424
10°	100894
15°	100162
20°	99053
25°	97489
30°	94628
35°	90173
40°	83519
45°	70080
50°	46332
55°	22876
60°	9078
65°	3532
70°	541
75°	0
80°	0
85°	0



TEST NUMBER: P251398

CATALOG NUMBER: LSR8B60D010 EC8B60835 8LBS0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.0	5.5
10°-20°	884.4	15.6
20°-30°	1316.4	23.2
30°-40°	1490.9	26.2
40°-50°	1205.4	21.2
50°-60°	418.1	7.4
60°-70°	57.2	1.0
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2511.7	44.2
0°-40°	4002.6	70.4
0°-60°	5626.0	99.0
0°-90°	5684.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5684.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3293	
5°	3277	311
15°	3138	884
25°	2865	1316
35°	2395	1491
45°	1607	1205
55°	426	418
65°	48	57
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P251398

CATALOG NUMBER: LSR8B60D010 EC8B60835 8LBS0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3292.7
2.5°	3288.7
5°	3276.6
7.5°	3252.4
10°	3222.2
12.5°	3181.8
15°	3137.5
17.5°	3081.0
20°	3018.5
22.5°	2945.9
25°	2865.3
27.5°	2768.5
30°	2657.6
32.5°	2532.6
35°	2395.4
37.5°	2244.2
40°	2074.8
42.5°	1867.2
45°	1607.0
47.5°	1292.5
50°	965.8
52.5°	661.4
55°	425.5
57.5°	252.0
60°	147.2
62.5°	86.7
65°	48.4
67.5°	22.2
70°	6.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)