

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250389

Luminaire Tested: **LSR8B120D010 EC8B120835 8LBN0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250389
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B120D010 EC8B120835 8LBN0B
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3500 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7281.0 lumens
Efficiency: N/A
Efficacy: 61.5 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250389

CATALOG NUMBER: LSR8B120D010 EC8B120835 8LBN0B

Luminous Intensity Polar Plot





TEST NUMBER: P250389

CATALOG NUMBER: LSR8B120D010 EC8B120835 8LBN0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72	79	75	71	77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	358759
5°	353028
10°	313656
15°	258738
20°	217910
25°	183795
30°	137616
35°	77882
40°	30794
45°	8268
50°	1583
55°	0
60°	228
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250389

CATALOG NUMBER: LSR8B120D010 EC8B120835 8LBN0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1044.4	14.3
10°-20°	2270.0	31.2
20°-30°	2437.0	33.5
30°-40°	1317.1	18.1
40°-50°	205.5	2.8
50°-60°	5.6	0.1
60°-70°	1.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5751.4	79.0
0°-40°	7068.5	97.1
0°-60°	7279.6	100.0
0°-90°	7281.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7281.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11634	
5°	11405	###
15°	8105	2270
25°	5402	2437
35°	2069	1317
45°	190	205
55°	0	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250389

CATALOG NUMBER: LSR8B120D010 EC8B120835 8LBN0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	11634.3
1°	11656.4
2°	11645.5
3°	11605.6
4°	11529.0
5°	11404.9
6°	11234.0
7°	11004.2
8°	10716.5
9°	10385.4
10°	10017.1
11°	9630.9
12°	9230.3
13°	8829.9
14°	8458.0
15°	8104.8
16°	7780.6
17°	7467.3
18°	7175.8
19°	6903.0
20°	6640.5
21°	6385.4
22°	6144.8
23°	5904.8
24°	5653.5
25°	5401.9
26°	5146.9
27°	4855.6
28°	4534.9
29°	4207.5
30°	3864.9
31°	3497.0
32°	3128.8
33°	2764.7
34°	2396.8
35°	2068.9
37.5°	1322.2
40°	765.0
42.5°	408.1
45°	189.6
47.5°	102.2
50°	33.0
52.5°	3.7
55°	0.0
57.5°	3.7



TEST NUMBER: P250389

CATALOG NUMBER: LSR8B120D010 EC8B120835 8LBN0B

CANDELA DISTRIBUTION (continued):

	0°
60°	3.7
62.5°	0.0
65°	0.0
67.5°	3.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)