

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247057

Luminaire Tested: **LSR8B120D010 EC8B120835 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247057
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25264)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B120D010 EC8B120835 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3500 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13133.0 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.22
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247057

CATALOG NUMBER: LSR8B120D010 EC8B120835 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P247057

CATALOG NUMBER: LSR8B120D010 EC8B120835 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	94	92
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	75	71	79	74	70	77	73	70	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	60	54	49	59	53	49	58	52	48	57	52	48	47
9	68	56	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	225984
5°	230391
10°	240273
15°	253851
20°	263366
25°	265279
30°	252736
35°	222929
40°	179710
45°	127592
50°	76680
55°	34547
60°	8906
65°	1919
70°	947
75°	631
80°	320
85°	0



TEST NUMBER: P247057

CATALOG NUMBER: LSR8B120D010 EC8B120835 8LBWOLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	718.0	5.5
10°-20°	2248.1	17.1
20°-30°	3555.3	27.1
30°-40°	3653.2	27.8
40°-50°	2266.1	17.3
50°-60°	642.5	4.9
60°-70°	43.4	0.3
70°-80°	5.8	0.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6521.4	49.7
0°-40°	10174.5	77.5
0°-60°	13083.1	99.6
0°-90°	13133.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13133.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7328	
5°	7443	718
15°	7952	2248
25°	7797	3555
35°	5922	3653
45°	2926	2266
55°	643	642
65°	26	43
75°	5	6
85°	0	1
90°	0	



TEST NUMBER: P247057

CATALOG NUMBER: LSR8B120D010 EC8B120835 8LBW0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7328.5
2.5°	7342.5
5°	7443.0
7.5°	7560.9
10°	7673.5
12.5°	7812.6
15°	7951.7
17.5°	8030.9
20°	8025.7
22.5°	7948.1
25°	7796.8
27.5°	7522.2
30°	7098.0
32.5°	6539.9
35°	5922.0
37.5°	5223.2
40°	4464.4
42.5°	3675.6
45°	2925.8
47.5°	2228.7
50°	1598.4
52.5°	1075.7
55°	642.6
57.5°	331.0
60°	144.4
62.5°	58.1
65°	26.3
67.5°	15.8
70°	10.5
72.5°	7.1
75°	5.3
77.5°	3.6
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)