

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250480

Luminaire Tested: **LSR8B120D010 EC8B120840 8LBM0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250480
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14005)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B120D010 EC8B120840 8LBM0GPH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 4000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10719.1 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250480

CATALOG NUMBER: LSR8B120D010 EC8B120840 8LBM0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250480

CATALOG NUMBER: LSR8B120D010 EC8B120840 8LBM0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	419204
5°	408607
10°	366294
15°	326236
20°	297609
25°	270396
30°	221719
35°	145916
40°	72791
45°	27094
50°	8227
55°	995
60°	574
65°	0
70°	424
75°	1668
80°	0
85°	1663



TEST NUMBER: P250480

CATALOG NUMBER: LSR8B120D010 EC8B120840 8LBM0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1210.3	11.3
10°-20°	2877.6	26.8
20°-30°	3585.1	33.4
30°-40°	2418.2	22.6
40°-50°	571.8	5.3
50°-60°	41.8	0.4
60°-70°	7.5	0.1
70°-80°	5.5	0.1
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7673.0	71.6
0°-40°	10091.2	94.1
0°-60°	10704.8	99.9
0°-90°	10719.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10719.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13594	
5°	13200	###
15°	10219	2878
25°	7947	3585
35°	3876	2418
45°	621	572
55°	18	42
65°	0	7
75°	14	6
85°	5	1
90°	0	



TEST NUMBER: P250480

CATALOG NUMBER: LSR8B120D010 EC8B120840 8LBM0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	13594.5
2.5°	13571.4
5°	13200.4
7.5°	12528.1
10°	11698.2
12.5°	10914.6
15°	10219.1
17.5°	9620.9
20°	9069.2
22.5°	8540.6
25°	7947.2
27.5°	7172.9
30°	6226.9
32.5°	5081.8
35°	3876.2
37.5°	2772.7
40°	1808.3
42.5°	1080.4
45°	621.3
47.5°	347.7
50°	171.5
52.5°	78.8
55°	18.5
57.5°	4.7
60°	9.3
62.5°	14.0
65°	0.0
67.5°	9.3
70°	4.7
72.5°	4.7
75°	14.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	4.7
87.5°	0.0
90°	0.0

(END OF REPORT)