

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251444

Luminaire Tested: **LSR8B60D010 EC8B60840 8LBN0MW**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251444  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B60D010 EC8B60840 8LBN0MW  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 4000 CCT WITH MATTE WHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5706.0 lumens  
Efficiency: N/A  
Efficacy: 95.9 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251444

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBN0MW

### Luminous Intensity Polar Plot





TEST NUMBER: P251444

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBN0MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98		98	97	95		95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71		78	74	70		76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65		73	68	64		71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55		64	59	55		63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53	48	45	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	184518
5°	183196
10°	166943
15°	143093
20°	126815
25°	113164
30°	91392
35°	63412
40°	40234
45°	29885
50°	25507
55°	22365
60°	20013
65°	17884
70°	15408
75°	14178
80°	13212
85°	11640



TEST NUMBER: P251444

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBN0MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	545.9	9.6
10°-20°	1262.6	22.1
20°-30°	1501.5	26.3
30°-40°	1061.5	18.6
40°-50°	547.9	9.6
50°-60°	375.6	6.6
60°-70°	243.8	4.3
70°-80°	127.9	2.2
80°-90°	39.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3310.0	58.0
0°-40°	4371.4	76.6
0°-60°	5294.9	92.8
0°-90°	5706.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5706.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5984	
5°	5918	546
15°	4482	1263
25°	3326	1501
35°	1684	1061
45°	685	548
55°	416	376
65°	245	244
75°	119	128
85°	33	37
90°	0	3
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251444

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBN0MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5983.8
2.5°	5983.8
5°	5918.3
7.5°	5700.7
10°	5331.6
12.5°	4891.3
15°	4482.3
17.5°	4145.7
20°	3864.5
22.5°	3598.6
25°	3326.0
27.5°	2984.0
30°	2566.7
32.5°	2117.8
35°	1684.5
37.5°	1297.8
40°	999.5
42.5°	804.3
45°	685.3
47.5°	598.9
50°	531.7
52.5°	472.8
55°	416.0
57.5°	365.9
60°	324.5
62.5°	281.2
65°	245.1
67.5°	212.3
70°	170.9
72.5°	146.8
75°	119.0
77.5°	96.6
80°	74.4
82.5°	55.3
85°	32.9
87.5°	19.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251444

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBN0MW

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)