

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251038

Luminaire Tested: **LSR8B60D010 EC8B60840 8LBN0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251038
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201884)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B60840 8LBN0WMH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 4000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5445.1 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251038

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBN0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P251038

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBN0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75	81	77	74	80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62	70	65	62	69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59	66	62	59	65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56	63	59	55	62	58	55	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	244523
5°	241114
10°	220615
15°	189412
20°	159499
25°	131752
30°	98848
35°	58917
40°	28061
45°	12228
50°	5517
55°	2425
60°	1437
65°	788
70°	811
75°	0
80°	320
85°	1309



TEST NUMBER: P251038

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBN0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	719.4	13.2
10°-20°	1653.3	30.4
20°-30°	1754.1	32.2
30°-40°	1000.9	18.4
40°-50°	248.1	4.6
50°-60°	48.7	0.9
60°-70°	14.6	0.3
70°-80°	3.3	0.1
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4126.7	75.8
0°-40°	5127.6	94.2
0°-60°	5424.4	99.6
0°-90°	5445.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5445.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7930	
5°	7789	719
15°	5933	1653
25°	3872	1754
35°	1565	1001
45°	280	248
55°	45	49
65°	11	15
75°	0	3
85°	4	3
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251038

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBN0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	7929.7
2.5°	7926.0
5°	7789.4
7.5°	7489.3
10°	7045.7
12.5°	6510.0
15°	5933.2
17.5°	5383.5
20°	4860.5
22.5°	4357.6
25°	3872.3
27.5°	3351.1
30°	2776.1
32.5°	2157.9
35°	1565.1
37.5°	1078.2
40°	697.1
42.5°	442.0
45°	280.4
47.5°	183.4
50°	115.0
52.5°	69.9
55°	45.1
57.5°	36.1
60°	23.3
62.5°	21.6
65°	10.8
67.5°	10.8
70°	9.0
72.5°	5.3
75°	0.0
77.5°	1.8
80°	1.8
82.5°	3.7
85°	3.7
87.5°	1.8
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251038

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBN0WMH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)