

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251290

Luminaire Tested: **LSR8B60D010 EC8B60840 8LBSOGPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251290
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B60840 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 4000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6137.0 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251290

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P251290

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61		70	65	61		68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50		59	54	50		58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	108624
5°	108296
10°	107228
15°	106128
20°	105016
25°	103297
30°	100471
35°	95891
40°	89158
45°	75282
50°	51110
55°	26703
60°	11983
65°	5844
70°	2344
75°	1430
80°	1065
85°	708



TEST NUMBER: P251290

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	331.6	5.4
10°-20°	937.7	15.3
20°-30°	1395.9	22.7
30°-40°	1586.7	25.9
40°-50°	1297.5	21.1
50°-60°	483.7	7.9
60°-70°	88.4	1.4
70°-80°	13.7	0.2
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2665.1	43.4
0°-40°	4251.8	69.3
0°-60°	6033.0	98.3
0°-90°	6137.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6137.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3523	
5°	3499	332
15°	3324	938
25°	3036	1396
35°	2547	1587
45°	1726	1297
55°	497	484
65°	80	88
75°	12	14
85°	2	2
90°	0	



TEST NUMBER: P251290

CATALOG NUMBER: LSR8B60D010 EC8B60840 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3522.6
2.5°	3516.6
5°	3498.6
7.5°	3466.6
10°	3424.5
12.5°	3376.4
15°	3324.4
17.5°	3264.3
20°	3200.2
22.5°	3124.1
25°	3036.0
27.5°	2935.9
30°	2821.7
32.5°	2691.5
35°	2547.3
37.5°	2393.1
40°	2214.9
42.5°	1994.6
45°	1726.3
47.5°	1403.8
50°	1065.4
52.5°	751.0
55°	496.7
57.5°	312.4
60°	194.3
62.5°	124.2
65°	80.1
67.5°	46.1
70°	26.0
72.5°	16.0
75°	12.0
77.5°	8.0
80°	6.0
82.5°	2.0
85°	2.0
87.5°	0.0
90°	0.0

(END OF REPORT)