

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247041

Luminaire Tested: **LSR8B120D010 EC8B120927 8LBNOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247041
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-80)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B120D010 EC8B120927 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 2700 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9194.6 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 0.47 / 0.47 / 0.56
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247041

CATALOG NUMBER: LSR8B120D010 EC8B120927 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P247041

CATALOG NUMBER: LSR8B120D010 EC8B120927 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95	95		
2	110	105	102	99	107	104	100	98	100	98	96	98	95	94	95	93	92	90	90	90	90	90		
3	105	100	95	92	103	98	94	91	96	92	90	93	91	88	91	89	87	85	85	85	85	85		
4	101	94	90	86	99	93	89	85	91	87	84	89	86	83	87	85	83	81	81	81	81	81		
5	97	90	85	81	95	89	84	80	87	83	80	85	82	79	84	81	78	77	77	77	77	77		
6	93	85	80	76	91	84	80	76	83	79	76	82	78	75	80	77	75	73	73	73	73	73		
7	89	81	76	72	88	81	76	72	79	75	72	78	74	72	77	74	71	70	70	70	70	70		
8	86	78	72	69	85	77	72	69	76	72	69	75	71	68	74	71	68	67	67	67	67	67		
9	82	74	69	66	81	74	69	66	73	69	65	72	68	65	71	68	65	64	64	64	64	64		
10	79	71	66	63	79	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61	61		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P247041

CATALOG NUMBER: LSR8B120D010 EC8B120927 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1915.7	20.8
10°-20°	3168.1	34.5
20°-30°	2670.9	29.0
30°-40°	1211.9	13.2
40°-50°	211.6	2.3
50°-60°	11.5	0.1
60°-70°	1.7	0.0
70°-80°	1.9	0.0
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7754.7	84.3
0°-40°	8966.6	97.5
0°-60°	9189.7	99.9
0°-90°	9194.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9194.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	23358	
5°	22031	###
15°	11182	3168
25°	5887	2671
35°	1862	1212
45°	230	212
55°	9	12
65°	4	2
75°	0	2
85°	1	1
90°	0	



TEST NUMBER: P247041

CATALOG NUMBER: LSR8B120D010 EC8B120927 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	23357.9
2.5°	23151.4
5°	22031.0
7.5°	19590.5
10°	16402.4
12.5°	13455.3
15°	11182.3
17.5°	9474.5
20°	8109.4
22.5°	6908.3
25°	5887.1
27.5°	4848.6
30°	3761.7
32.5°	2738.1
35°	1862.3
37.5°	1143.4
40°	672.8
42.5°	394.7
45°	229.6
47.5°	137.4
50°	53.1
52.5°	8.1
55°	9.2
57.5°	8.1
60°	1.1
62.5°	1.1
65°	3.5
67.5°	0.0
70°	3.5
72.5°	5.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	1.1
87.5°	3.5
90°	0.0

(END OF REPORT)