

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246997

Luminaire Tested: **LSR8B120D010 EC8B120930 8LBM0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246997
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-81)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B120D010 EC8B120930 8LBMOLI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10464.5 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.75
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246997

CATALOG NUMBER: LSR8B120D010 EC8B120930 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P246997

CATALOG NUMBER: LSR8B120D010 EC8B120930 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100		
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94	94		
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88	88	88	88	88		
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83	83	83	83	83		
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78	78	78	78	78		
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73	73	73	73	73		
6	90	82	76	72	89	81	76	72	79	75	71	78	74	71	77	73	70	69	69	69	69	69		
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65	65	65	65	65		
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	62	62	62	62	62		
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58	58	58	58	58		
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	55	55	55	55	55		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P246997

CATALOG NUMBER: LSR8B120D010 EC8B120930 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1496.7	14.3
10°-20°	3281.0	31.4
20°-30°	3346.1	32.0
30°-40°	1874.0	17.9
40°-50°	399.6	3.8
50°-60°	49.5	0.5
60°-70°	12.9	0.1
70°-80°	3.1	0.0
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8123.7	77.6
0°-40°	9997.8	95.5
0°-60°	10446.9	99.8
0°-90°	10464.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10464.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17173	
5°	16394	###
15°	11812	3281
25°	7376	3346
35°	2971	1874
45°	444	400
55°	38	50
65°	15	13
75°	5	3
85°	5	2
90°	0	



TEST NUMBER: P246997

CATALOG NUMBER: LSR8B120D010 EC8B120930 8LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	17172.6
2.5°	16979.2
5°	16394.1
7.5°	15452.4
10°	14290.6
12.5°	13043.7
15°	11812.5
17.5°	10574.2
20°	9435.5
22.5°	8375.9
25°	7375.8
27.5°	6326.0
30°	5217.7
32.5°	4059.6
35°	2970.8
37.5°	1990.2
40°	1237.2
42.5°	739.6
45°	444.0
47.5°	247.0
50°	144.7
52.5°	76.7
55°	37.7
57.5°	26.8
60°	23.1
62.5°	11.0
65°	14.6
67.5°	14.6
70°	1.2
72.5°	3.7
75°	4.8
77.5°	2.5
80°	0.0
82.5°	1.2
85°	4.8
87.5°	0.0
90°	0.0

(END OF REPORT)