

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247045

Luminaire Tested: **LSR8B120D010 EC8B120930 8LBNOLI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247045  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-80)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B120D010 EC8B120930 8LBN0LI  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9693.2 lumens  
Efficiency: N/A  
Efficacy: 81.9 lumens/watt  
Spacing Criteria (0/90/45): 0.47 / 0.47 / 0.56  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 118.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P247045

CATALOG NUMBER: LSR8B120D010 EC8B120930 8LBN0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P247045

CATALOG NUMBER: LSR8B120D010 EC8B120930 8LBN0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95
2	110	105	102	99	107	104	100	98	100	98	96	98	95	94	95	93	92	90	90	90
3	105	100	95	92	103	98	94	91	96	92	90	93	91	88	91	89	87	85	85	85
4	101	94	90	86	99	93	89	85	91	87	84	89	86	83	87	85	83	81	81	81
5	97	90	85	81	95	89	84	80	87	83	80	85	82	79	84	81	78	77	77	77
6	93	85	80	76	91	84	80	76	83	79	76	82	78	75	80	77	75	73	73	73
7	89	81	76	72	88	81	76	72	79	75	72	78	74	72	77	74	71	70	70	70
8	86	78	72	69	85	77	72	69	76	72	69	75	71	68	74	71	68	67	67	67
9	82	74	69	66	81	74	69	66	73	69	65	72	68	65	71	68	65	64	64	64
10	79	71	66	63	79	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P247045

CATALOG NUMBER: LSR8B120D010 EC8B120930 8LBN0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2019.6	20.8
10°-20°	3339.9	34.5
20°-30°	2815.7	29.0
30°-40°	1277.7	13.2
40°-50°	223.0	2.3
50°-60°	12.1	0.1
60°-70°	1.8	0.0
70°-80°	2.1	0.0
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8175.2	84.3
0°-40°	9452.9	97.5
0°-60°	9688.0	99.9
0°-90°	9693.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9693.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	24625	
5°	23226	###
15°	11789	3340
25°	6206	2816
35°	1963	1278
45°	242	223
55°	10	12
65°	4	2
75°	0	2
85°	1	1
90°	0	



TEST NUMBER: P247045

CATALOG NUMBER: LSR8B120D010 EC8B120930 8LBN0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	24624.7
2.5°	24407.0
5°	23225.8
7.5°	20653.0
10°	17291.9
12.5°	14185.1
15°	11788.7
17.5°	9988.3
20°	8549.3
22.5°	7282.9
25°	6206.3
27.5°	5111.5
30°	3965.6
32.5°	2886.7
35°	1963.3
37.5°	1205.5
40°	709.1
42.5°	416.0
45°	242.0
47.5°	144.7
50°	55.9
52.5°	8.5
55°	9.8
57.5°	8.5
60°	1.2
62.5°	1.2
65°	3.7
67.5°	0.0
70°	3.7
72.5°	6.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	1.2
87.5°	3.7
90°	0.0

(END OF REPORT)