

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251336

Luminaire Tested: **LSR8B60D010 EC8B60850 8LBW0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251336  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B60D010 EC8B60850 8LBW0B  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 5000 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4021.0 lumens  
Efficiency: N/A  
Efficacy: 67.6 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251336

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBW0B

### Luminous Intensity Polar Plot





TEST NUMBER: P251336

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBW0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80
4	96	88	83	78	94	87	82	78	85	80	77	83	79	76	81	78	75	74
5	91	82	76	72	89	81	76	71	80	75	71	78	74	70	76	73	70	68
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	65	63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58
8	77	67	61	57	76	67	61	57	66	60	56	65	60	56	64	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51
10	70	59	53	49	68	59	53	49	58	53	49	57	52	49	57	52	49	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	113385
5°	110534
10°	107591
15°	105589
20°	102840
25°	99197
30°	91018
35°	69785
40°	33201
45°	12642
50°	6169
55°	2527
60°	629
65°	146
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P251336

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBW0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	336.6	8.4
10°-20°	930.7	23.1
20°-30°	1329.0	33.1
30°-40°	1101.4	27.4
40°-50°	271.6	6.8
50°-60°	48.9	1.2
60°-70°	2.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2596.4	64.6
0°-40°	3697.8	92.0
0°-60°	4018.3	99.9
0°-90°	4021.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4021.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3677	
5°	3571	337
15°	3308	931
25°	2916	1329
35°	1854	1101
45°	290	272
55°	47	49
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P251336

CATALOG NUMBER: LSR8B60D010 EC8B60850 8LBW0B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3677.0
2.5°	3646.4
5°	3570.9
7.5°	3497.4
10°	3436.1
12.5°	3376.9
15°	3307.5
17.5°	3225.8
20°	3133.9
22.5°	3029.8
25°	2915.5
27.5°	2760.3
30°	2556.2
32.5°	2268.3
35°	1853.8
37.5°	1339.3
40°	824.8
42.5°	479.8
45°	289.9
47.5°	191.9
50°	128.6
52.5°	83.7
55°	47.0
57.5°	22.5
60°	10.2
62.5°	4.1
65°	2.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)