

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250438

Luminaire Tested: **LSR8B120D010 EC8B120950 8LBN0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250438  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B120D010 EC8B120950 8LBN0B  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 5000 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6714.0 lumens  
Efficiency: N/A  
Efficacy: 56.8 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 118.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250438

CATALOG NUMBER: LSR8B120D010 EC8B120950 8LBN0B

### Luminous Intensity Polar Plot





TEST NUMBER: P250438

CATALOG NUMBER: LSR8B120D010 EC8B120950 8LBN0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72	79	75	71	77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	330821
5°	325535
10°	289232
15°	238591
20°	200941
25°	169484
30°	126899
35°	71818
40°	28395
45°	7623
50°	1458
55°	0
60°	210
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250438

CATALOG NUMBER: LSR8B120D010 EC8B120950 8LBN0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	963.1	14.3
10°-20°	2093.2	31.2
20°-30°	2247.2	33.5
30°-40°	1214.6	18.1
40°-50°	189.5	2.8
50°-60°	5.2	0.1
60°-70°	1.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5303.5	79.0
0°-40°	6518.1	97.1
0°-60°	6712.7	100.0
0°-90°	6714.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6714.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10728	
5°	10517	963
15°	7474	2093
25°	4981	2247
35°	1908	1215
45°	175	189
55°	0	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250438

CATALOG NUMBER: LSR8B120D010 EC8B120950 8LBN0B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10728.3
1°	10748.7
2°	10738.6
3°	10701.8
4°	10631.2
5°	10516.7
6°	10359.2
7°	10147.2
8°	9881.9
9°	9576.6
10°	9237.1
11°	8880.9
12°	8511.5
13°	8142.3
14°	7799.4
15°	7473.7
16°	7174.7
17°	6885.8
18°	6617.0
19°	6365.4
20°	6123.4
21°	5888.2
22°	5666.3
23°	5445.0
24°	5213.2
25°	4981.3
26°	4746.1
27°	4477.5
28°	4181.7
29°	3879.8
30°	3563.9
31°	3224.7
32°	2885.2
33°	2549.4
34°	2210.2
35°	1907.8
37.5°	1219.3
40°	705.4
42.5°	376.3
45°	174.8
47.5°	94.3
50°	30.4
52.5°	3.4
55°	0.0
57.5°	3.4



TEST NUMBER: P250438

CATALOG NUMBER: LSR8B120D010 EC8B120950 8LBN0B

**CANDELA DISTRIBUTION (continued):**

	0°
60°	3.4
62.5°	0.0
65°	0.0
67.5°	3.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)