

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250445

Luminaire Tested: **LSR8B120D010 EC8B1209727 8LBN0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250445  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B120D010 EC8B1209727 8LBN0B  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 2700 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5070.0 lumens  
Efficiency: N/A  
Efficacy: 42.9 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 118.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250445

CATALOG NUMBER: LSR8B120D010 EC8B1209727 8LBN0B

### Luminous Intensity Polar Plot





TEST NUMBER: P250445

CATALOG NUMBER: LSR8B120D010 EC8B1209727 8LBN0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P250445

CATALOG NUMBER: LSR8B120D010 EC8B1209727 8LBN0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	727.3	14.3
10°-20°	1580.7	31.2
20°-30°	1696.9	33.5
30°-40°	917.2	18.1
40°-50°	143.1	2.8
50°-60°	3.9	0.1
60°-70°	1.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4004.9	79.0
0°-40°	4922.0	97.1
0°-60°	5069.0	100.0
0°-90°	5070.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5070.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8101	
5°	7942	727
15°	5644	1581
25°	3762	1697
35°	1441	917
45°	132	143
55°	0	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250445

CATALOG NUMBER: LSR8B120D010 EC8B1209727 8LBN0B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8101.4
1°	8116.7
2°	8109.1
3°	8081.3
4°	8028.0
5°	7941.6
6°	7822.6
7°	7662.6
8°	7462.2
9°	7231.7
10°	6975.3
11°	6706.3
12°	6427.3
13°	6148.6
14°	5889.6
15°	5643.7
16°	5417.9
17°	5199.7
18°	4996.8
19°	4806.8
20°	4624.0
21°	4446.4
22°	4278.9
23°	4111.7
24°	3936.7
25°	3761.5
26°	3583.9
27°	3381.1
28°	3157.8
29°	2929.8
30°	2691.2
31°	2435.1
32°	2178.7
33°	1925.1
34°	1669.0
35°	1440.6
37.5°	920.7
40°	532.7
42.5°	284.2
45°	132.0
47.5°	71.2
50°	23.0
52.5°	2.6
55°	0.0
57.5°	2.6



TEST NUMBER: P250445

CATALOG NUMBER: LSR8B120D010 EC8B1209727 8LBN0B

**CANDELA DISTRIBUTION (continued):**

	0°
60°	2.6
62.5°	0.0
65°	0.0
67.5°	2.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)