

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247761

Luminaire Tested: **LSR8B120D010 EC8B1209727 8LBS0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247761
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-88)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B120D010 EC8B1209727 8LBS0MW
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 2700 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9503.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.24
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247761

CATALOG NUMBER: LSR8B120D010 EC8B1209727 8LBS0MW

Luminous Intensity Polar Plot





TEST NUMBER: P247761

CATALOG NUMBER: LSR8B120D010 EC8B1209727 8LBS0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61
5	83	72	64	59	81	71	64	58	69	62	58	67	61	57	65	60	57	55
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49
7	72	60	52	47	70	59	52	47	58	51	47	57	51	46	55	50	46	44
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37
10	60	47	40	36	58	47	40	35	46	40	35	45	39	35	44	39	35	33

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P247761

CATALOG NUMBER: LSR8B120D010 EC8B1209727 8LBS0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	475.9	5.0
10°-20°	1343.4	14.1
20°-30°	1976.3	20.8
30°-40°	2232.3	23.5
40°-50°	1880.0	19.8
50°-60°	948.5	10.0
60°-70°	371.6	3.9
70°-80°	209.8	2.2
80°-90°	65.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3795.5	39.9
0°-40°	6027.8	63.4
0°-60°	8856.3	93.2
0°-90°	9503.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9503.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5046	
5°	5014	476
15°	4775	1343
25°	4300	1976
35°	3586	2232
45°	2476	1880
55°	1024	948
65°	360	372
75°	204	210
85°	58	65
90°	0	



TEST NUMBER: P247761

CATALOG NUMBER: LSR8B120D010 EC8B1209727 8LBS0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5046.2
2.5°	5041.1
5°	5014.4
7.5°	4979.5
10°	4920.0
12.5°	4846.2
15°	4775.4
17.5°	4667.7
20°	4560.0
22.5°	4443.1
25°	4300.5
27.5°	4139.5
30°	3971.3
32.5°	3782.6
35°	3585.7
37.5°	3360.0
40°	3131.3
42.5°	2819.5
45°	2475.9
47.5°	2082.1
50°	1692.3
52.5°	1340.5
55°	1023.6
57.5°	771.3
60°	580.5
62.5°	443.1
65°	360.0
67.5°	293.3
70°	238.0
72.5°	229.7
75°	204.1
77.5°	170.3
80°	143.6
82.5°	91.3
85°	58.5
87.5°	18.5
90°	0.0

(END OF REPORT)