

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251030

Luminaire Tested: **LSR8B60D010 EC8B60930 8LBW0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251030  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B60D010 EC8B60930 8LBW0WMH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 3000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4469.0 lumens  
Efficiency: N/A  
Efficacy: 75.1 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251030

CATALOG NUMBER: LSR8B60D010 EC8B60930 8LBW0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P251030

CATALOG NUMBER: LSR8B60D010 EC8B60930 8LBW0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91					91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83					83			
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75					75			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68					68			
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62					62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56					56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51					51			
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47					47			
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44					44			
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41					41			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P251030

CATALOG NUMBER: LSR8B60D010 EC8B60930 8LBW0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	297.4	6.7
10°-20°	827.3	18.5
20°-30°	1232.3	27.6
30°-40°	1144.4	25.6
40°-50°	540.5	12.1
50°-60°	290.4	6.5
60°-70°	116.6	2.6
70°-80°	18.3	0.4
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2356.9	52.7
0°-40°	3501.3	78.3
0°-60°	4332.3	96.9
0°-90°	4469.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4469.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3239	
5°	3162	297
15°	2928	827
25°	2697	1232
35°	1902	1144
45°	659	541
55°	319	290
65°	116	117
75°	15	18
85°	2	2
90°	0	



TEST NUMBER: P251030

CATALOG NUMBER: LSR8B60D010 EC8B60930 8LBW0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3238.7
2.5°	3216.4
5°	3161.5
7.5°	3091.7
10°	3026.4
12.5°	2972.9
15°	2928.4
17.5°	2882.3
20°	2831.8
22.5°	2773.9
25°	2696.7
27.5°	2588.3
30°	2438.3
32.5°	2218.5
35°	1902.2
37.5°	1498.3
40°	1110.8
42.5°	827.1
45°	659.3
47.5°	550.9
50°	464.8
52.5°	387.6
55°	319.3
57.5°	259.9
60°	210.9
62.5°	164.8
65°	115.8
67.5°	68.3
70°	40.1
72.5°	23.8
75°	14.8
77.5°	8.9
80°	4.5
82.5°	3.0
85°	1.5
87.5°	0.0
90°	0.0

(END OF REPORT)