

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250830

Luminaire Tested: **LSR8B60D010 EC8B60935 8LBN0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250830
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B60935 8LBNOLI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 3500 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5071.0 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250830
CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBNOLI

Luminous Intensity Polar Plot





TEST NUMBER: P250830

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBNOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | | 102 | 101 | 100 | | 99 | 98 | 97 | 95 |
| 2 | 110 | 106 | 102 | 100 | 108 | 104 | 101 | 99 | 101 | 99 | 96 | | 98 | 96 | 94 | | 95 | 94 | 92 | 91 |
| 3 | 106 | 100 | 96 | 93 | 104 | 99 | 95 | 92 | 96 | 93 | 91 | | 94 | 92 | 89 | | 92 | 90 | 88 | 87 |
| 4 | 102 | 95 | 91 | 87 | 100 | 94 | 90 | 87 | 92 | 89 | 86 | | 90 | 87 | 85 | | 89 | 86 | 84 | 83 |
| 5 | 98 | 91 | 86 | 83 | 96 | 90 | 86 | 82 | 88 | 85 | 82 | | 87 | 84 | 81 | | 85 | 83 | 80 | 79 |
| 6 | 94 | 87 | 82 | 79 | 93 | 86 | 82 | 78 | 85 | 81 | 78 | | 83 | 80 | 77 | | 82 | 79 | 77 | 76 |
| 7 | 91 | 83 | 78 | 75 | 90 | 83 | 78 | 75 | 81 | 77 | 74 | | 80 | 77 | 74 | | 79 | 76 | 74 | 72 |
| 8 | 88 | 80 | 75 | 72 | 86 | 79 | 75 | 71 | 78 | 74 | 71 | | 77 | 74 | 71 | | 76 | 73 | 71 | 70 |
| 9 | 85 | 77 | 72 | 69 | 84 | 76 | 72 | 69 | 75 | 71 | 68 | | 75 | 71 | 68 | | 74 | 70 | 68 | 67 |
| 10 | 82 | 74 | 69 | 66 | 81 | 73 | 69 | 66 | 73 | 69 | 66 | | 72 | 68 | 66 | | 71 | 68 | 65 | 64 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 766113 |
| 5° | 532104 |
| 10° | 280005 |
| 15° | 177163 |
| 20° | 131658 |
| 25° | 103508 |
| 30° | 74521 |
| 35° | 31979 |
| 40° | 11146 |
| 45° | 4274 |
| 50° | 988 |
| 55° | 371 |
| 60° | 0 |
| 65° | 503 |
| 70° | 153 |
| 75° | 405 |
| 80° | 604 |
| 85° | 0 |



TEST NUMBER: P250830

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBNOLI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 1378.1 | 27.2 |
| 10°-20° | 1601.2 | 31.6 |
| 20°-30° | 1382.0 | 27.3 |
| 30°-40° | 599.5 | 11.8 |
| 40°-50° | 94.0 | 1.9 |
| 50°-60° | 6.8 | 0.1 |
| 60°-70° | 3.7 | 0.1 |
| 70°-80° | 3.8 | 0.1 |
| 80°-90° | 1.9 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 4361.3 | 86.0 |
| 0°-40° | 4960.9 | 97.8 |
| 0°-60° | 5061.6 | 99.8 |
| 0°-90° | 5071.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 5071.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 24844 | |
| 5° | 17190 | ### |
| 15° | 5550 | 1601 |
| 25° | 3042 | 1382 |
| 35° | 850 | 600 |
| 45° | 98 | 94 |
| 55° | 7 | 7 |
| 65° | 7 | 4 |
| 75° | 3 | 4 |
| 85° | 0 | 2 |
| 90° | 0 | |



TEST NUMBER: P250830

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBNOLI

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|---------|
| 0° | 24844.5 |
| 2.5° | 22435.2 |
| 5° | 17190.1 |
| 7.5° | 12259.8 |
| 10° | 8942.4 |
| 12.5° | 6861.6 |
| 15° | 5549.5 |
| 17.5° | 4667.3 |
| 20° | 4012.1 |
| 22.5° | 3453.2 |
| 25° | 3042.2 |
| 27.5° | 2608.8 |
| 30° | 2092.9 |
| 32.5° | 1454.9 |
| 35° | 849.5 |
| 37.5° | 474.6 |
| 40° | 276.9 |
| 42.5° | 172.0 |
| 45° | 98.0 |
| 47.5° | 79.1 |
| 50° | 20.6 |
| 52.5° | 10.3 |
| 55° | 6.9 |
| 57.5° | 3.4 |
| 60° | 0.0 |
| 62.5° | 1.7 |
| 65° | 6.9 |
| 67.5° | 5.2 |
| 70° | 1.7 |
| 72.5° | 8.6 |
| 75° | 3.4 |
| 77.5° | 0.0 |
| 80° | 3.4 |
| 82.5° | 1.7 |
| 85° | 0.0 |
| 87.5° | 3.4 |
| 90° | 0.0 |

(END OF REPORT)