

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244459

Luminaire Tested: **LSR8B15D010 EC8B15835 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244459
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B15D010 EC8B15835 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3500 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1673.0 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244459

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P244459

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBS0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69		76	72	68		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56		65	59	55		63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50		60	54	50		59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46		55	50	46		54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29939
5°	29840
10°	29612
15°	29405
20°	29206
25°	28822
30°	27930
35°	26351
40°	23951
45°	19707
50°	13135
55°	6844
60°	3225
65°	1693
70°	847
75°	584
80°	444
85°	354



TEST NUMBER: P244459

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBS0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	5.5
10°-20°	260.0	15.5
20°-30°	388.9	23.2
30°-40°	435.0	26.0
40°-50°	341.3	20.4
50°-60°	124.5	7.4
60°-70°	25.4	1.5
70°-80°	5.5	0.3
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	740.3	44.2
0°-40°	1175.3	70.2
0°-60°	1641.0	98.1
0°-90°	1673.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1673.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	971	
5°	964	91
15°	921	260
25°	847	389
35°	700	435
45°	452	341
55°	127	125
65°	23	25
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P244459

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBS0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	970.9
2.5°	969.4
5°	964.0
7.5°	956.1
10°	945.7
12.5°	933.9
15°	921.1
17.5°	906.8
20°	890.0
22.5°	870.2
25°	847.1
27.5°	818.4
30°	784.4
32.5°	744.4
35°	700.0
37.5°	650.2
40°	595.0
42.5°	529.4
45°	451.9
47.5°	364.6
50°	273.8
52.5°	191.9
55°	127.3
57.5°	81.4
60°	52.3
62.5°	34.5
65°	23.2
67.5°	14.8
70°	9.4
72.5°	6.4
75°	4.9
77.5°	3.5
80°	2.5
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)